

# FOR GENERAL USE

## NO.6 Combination Auger Bit




As contrasted to the bits used in the past, this bit is equipped with an axis usable with an electric drill and is handy for people who require speed.



Size 39m/m ~

For reduced the drilling resistance.



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz	Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz
3	110	60	6.35	0.20	27 (1-1/16)	210	140	10	3.74
4	120	70	6.35	0.24	28	210	140	10	4.20
5	140	90	6.35	0.28	29 (1-1/8)	210	140	10	4.21
6 (1/4)	160	100	6.35	0.39	30 (1-3/16)	210	140	10	4.32
7	170	100	6.35	0.52	31	210	140	12	5.04
8 (5/16)	170	100	6.35	0.57	32 (1-1/4)	210	140	12	5.16
9	180	110	6.35	0.65	33	210	140	12	5.52
10 (3/8)	190	120	6.35	0.76	34	210	140	12	5.64
11 (7/16)	190	120	6.35	0.81	35 (1-3/8)	210	140	12	5.76
12	190	120	6.35	0.97	36	210	140	12	6.24
13 (1/2)	190	120	6.35	1.10	37 (1-7/16)	210	140	12	6.36
14 (9/16)	200	130	10	1.46	38 (1-1/2)	210	140	12	6.48
15	200	130	10	1.56	39	210	140	12	6.60
16 (5/8)	200	130	10	1.70	40	210	140	12	6.72
17	200	130	10	1.72	41 (1-5/8)	210	140	12	6.84
18 (11/16)	200	130	10	1.86	42	210	140	12	6.96
19 (3/4)	200	130	10	1.98	43	210	140	12	7.08
20	210	140	10	2.56	44 (1-3/4)	210	140	12	7.44
21 (13/16)	210	140	10	2.78	45	210	140	12	7.56
22 (7/8)	210	140	10	2.90	46	210	140	12	7.68
23	210	140	10	3.04	47	210	140	12	8.04
24 (15/16)	210	140	10	3.26	48 (1-7/8)	210	140	12	9.00
25 (1" )	210	140	10	3.40	49	210	140	12	9.36
26	210	140	10	3.62	50 (2" )	210	140	12	9.60

### NO.5005 Drill Stopper (P.41)

Can be used with the Augers and to adjust the exact drilling depth.

