


FOR POWER TOOLS

NO.4 Power Drill Auger Bit



This is an item of the highest grade which withstands high speeds.
It maintains high precision, and eliminates lateral vibration.



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz	Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz
3	150	100	2.8	0.20	21 (13/16)	330	240	12	4.80
4	180	130	3.8	0.25	22 (7/8)	330	240	12	4.98
5	200	150	4.7	0.35	23	330	240	12	5.04
6 (1/4)	210	150	5.7	0.47	24 (15/16)	330	240	12	5.58
7	225	165	6.7	0.64	25 (1")	330	240	12	6.00
8 (5/16)	225	165	7	0.74	26	330	240	12	6.30
9	240	180	7	0.82	27 (1-1/16)	330	240	12	6.48
10 (3/8)	250	190	7	1.02	28	330	240	12	6.72
11 (7/16)	250	190	7	1.13	29 (1-1/8)	330	240	12	7.32
12	270	195	10	1.56	30 (1-3/16)	330	240	12	7.45
13 (1/2)	270	195	10	1.77	31	330	240	12	8.04
14 (9/16)	290	210	10	2.08	32 (1-1/4)	330	240	12	8.22
15	290	210	10	2.30	33	330	240	12	8.64
16 (5/8)	290	210	10	2.62	34	330	240	12	9.30
17	330	240	10	3.02	35 (1-3/8)	330	240	12	9.36
18 (11/16)	330	240	10	3.34	36	330	240	12	10.30
19 (3/4)	330	240	10	3.64	37 (1-7/16)	330	240	12	11.48
20	330	240	12	4.20	38 (1-1/2)	330	240	12	11.58

NO.4R Power Drill Auger Bit with depth marking

