


FOR POWER TOOLS


NO.4L Extra Long Power Auger Bit



This is an auger for deep boring which maintains high precision, and eliminates lateral vibration. When deep boring over 240m/m is required, use this long Power Auger Bit.



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia



OVERALL LENGTH 500L

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz
9	500	400	9	2.20
10 (3/8)	500	400	10	2.38
11 (7/16)	500	400	10	2.74
12	500	400	10	2.86
13 (1/2)	500	400	10	3.12
14 (9/16)	500	400	12	4.02
15	500	400	12	4.96
16 (5/8)	500	400	12	5.16
17	500	400	12	5.28
18 (11/16)	500	400	12	5.40
19 (3/4)	500	400	12	5.62
20	500	400	12	5.86
21 (13/16)	500	400	12	6.72
22 (7/8)	500	400	12	7.92
23	500	400	12	8.20
24 (15/16)	500	400	12	8.64
25 (1")	500	400	12	9.48
26	500	400	12	10.10
27 (1-1/16)	500	400	12	10.32
28	500	400	12	11.04
29 (1-1/8)	500	400	12	11.76
30 (1-3/16)	500	400	12	12.48

OVERALL LENGTH 400L

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz
9	400	300	9	1.72
10 (3/8)	400	300	10	1.98
11 (7/16)	400	300	10	2.24
12	400	300	10	2.44
13 (1/2)	400	300	10	2.55
14 (9/16)	400	300	12	3.12
15	400	300	12	3.42
16 (5/8)	400	300	12	3.96
17	400	300	12	4.05
18 (11/16)	400	300	12	4.32
19 (3/4)	400	300	12	4.52
20	400	300	12	4.76
21 (13/16)	400	300	12	4.92
22 (7/8)	400	300	12	6.36
23	400	300	12	6.70
24 (15/16)	400	300	12	7.08
25 (1")	400	300	12	7.68
26	400	300	12	8.22
27 (1-1/16)	400	300	12	8.76
28	400	300	12	8.82
29 (1-1/8)	400	300	12	8.88
30 (1-3/16)	400	300	12	9.60

OVERALL LENGTH 600L

Unit mm (inch)

Size	O/A Length	Twist Length	Shank-Dia	WT.kg/doz
9	600	500	9	2.28
10 (3/8)	600	500	10	2.84
11 (7/16)	600	500	10	3.12
12	600	500	10	3.44
13 (1/2)	600	500	10	3.96
14 (9/16)	600	500	12	4.14
15	600	500	12	4.68
16 (5/8)	600	500	12	6.00
17	600	500	12	6.20
18 (11/16)	600	500	12	6.48
19 (3/4)	600	500	12	6.68
20	600	500	12	6.92
21 (13/16)	600	500	12	8.76
22 (7/8)	600	500	12	9.00
23	600	500	12	9.85
24 (15/16)	600	500	12	10.62
25 (1")	600	500	12	11.04
26	600	500	12	11.90
27 (1-1/16)	600	500	12	12.72
28	600	500	12	13.70
29 (1-1/8)	600	500	12	13.92
30 (1-3/16)	600	500	12	14.28