


FOR SPECIAL USES

NO.5008 Triple Cutter

Three edges for light and quick chip ejection.



- ① Flat-bottom holes
- ② Curved holes
- ③ Through holes
- ④ Overlapped holes
- ⑤ Semicircular holes
- ⑥ Angled pocket holes



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia

Unit mm


Size	O/A Length	Twist Length	Shank-Dia	Size	O/A Length	Twist Length	Shank-Dia
10	130	28	6.35	23	130	28	6.35
12	130	28	6.35	24	130	28	6.35
13	130	28	6.35	25	130	28	6.35
15	130	28	6.35	26	130	28	8
16	130	28	6.35	27	130	28	8
18	130	28	6.35	28	130	28	8
19	130	28	6.35	30	130	28	8
20	130	28	6.35	32	130	28	9
21	130	28	6.35	33	130	28	9
22	130	28	6.35	35	130	28	9

FOR CONSTRUCTION WORK

NO.72/72-S Form-Tie Bit / with Stopper



NO.72
Form-Tie Bit



S=Size O/A=Overall Length T/L=Twist Length SD=Shank-Dia

Unit mm

Size	O/A Length	Twist Length	Shank-Dia
8	82	37	6.35
8.5	82	37	6.35
9	82	37	6.35
10	82	37	6.35
10.5	83	37	6.35
12	84	37	6.35
13.5	84	37	6.35
15	85	37	6.35

NO.72-S
Form-Tie Bit with Stopper

