

ベベルタイプ BS

芯押し台抜きナットに対応

パイプ等の大口径ワークに

振れ精度：0.003mm(T.I.R.)*1


MT 2 3 4 5 6

BS型




MT 2 3 4

BS型 60




総コロ



オイルシール

特長

- 1) 軸芯を太くし荷重に対する剛性をもたせ、高精度重切削用に最適
- 2) パイプや大内径ワークに対応 MT2～4は先端60°製品もラインナップ
- 3) オイルシールとOリングにより切削液、切粉などの侵入を防止



BS型 60



BS型



BS-B型
(MT.3, 4, 5のみ)

■ BS型 寸法表

型番	MT	A	B	C	M	L	D	d	α	重量 (kg)
BS2	2	32.5	19.5	68	4.5	120	70	20	75°	0.83
BS2-60		32	20				59	22	60°	0.70
BS3	3	42	21	85.5	5	148.5	84	20	75°	1.46
BS3-60		42.8	20.2				74	24.6	60°	1.28
BS3B	3	61	22	85.5	5	148.5	119	26	75°	3.31
BS4										3.61
BS4-60	4	58.9	24.2	107.8	6	190.8	98	30	60°	2.94
BS4B		8.16								
BS5	5	78	31	135.7	7	244.7	158	39	75°	9.02
BS5B										19.31
BS6	6	110	35	190	9.4	335	216	47.5	75°	20.81

■ 製品例：BS4B

