


フランジナット

FLANGED NUT

- 材質 S45C
- 熱処理 焼入 HRC30~40
- 仕上 黒染




品番	A	B	C	D	E	質量 (g)	メーカー希望小売価格
	ねじ径						
8MFN	M 8	19	13	12	3	10	330
10MFN	M10	22	17	13	3	21	350
12MFN	M12	28	19	17	4	35	360
14MFN	M14	28	22	17	4	41	410
16MFN	M16	33	24	20	5	60	440
18MFN	M18	35	27	20	5	71	510
20MFN	M20	40	30	25	6	112	670
22MFN	M22	45	32	28	6	147	1,040
24MFN	M24	47	36	28	6	176	1,260

座付球面フランジナット

SPHERICAL FLANGED NUT

- 材質 S45C
- 熱処理 焼入 HRC28~35
- 仕上 黒染




品番	A	B	C	D	E	F	質量 (g)	メーカー希望小売価格
	ねじ径							
8MSFN	M 8	19	13	11.5	2	4.5	20	710
10MSFN	M10	22	17	12	2	5	30	730
12MSFN	M12	28	19	16	3	6	54	830
14MSFN	M14	28	22	16	3	6.5	63	860
16MSFN	M16	35	24	18.5	3.5	7	96	990
18MSFN	M18	35	27	19	4	7.5	106	1,220
20MSFN	M20	40	30	23.5	4.5	8.5	161	1,420
22MSFN	M22	45	32	27	5	9	208	1,860
24MSFN	M24	48	36	27.5	5.5	9.5	270	2,120

カップリングナット

COUPLING NUT

- 材質 S45C
- 熱処理 焼入 HRC23~31
- 仕上 黒染




品番	A	B	C	質量 (g)	メーカー希望小売価格
	ねじ径				
FCU 8	M 8	13	24	18	380
FCU 10	M10	17	30	41	420
FCU 12	M12	19	36	57	480
FCU 14	M14	22	42	88	520
FCU 16	M16	24	48	113	650
FCU 18	M18	27	54	165	730
FCU 20	M20	30	60	226	780
FCU 22	M22	32	66	273	1,020
FCU 24	M24	36	72	392	1,480

カップリングナット

COUPLING NUT

- 材質 S45C
- 熱処理 焼入 HRC30~35
- 仕上 黒染




品番	A	B	C	質量 (g)	メーカー希望小売価格
	ねじ径				
8MCN	M 8	13	22	17	360
10MCN	M10	17	25	34	410
12MCN	M12	19	29	47	480
14MCN	M14	22	32	68	570
16MCN	M16	24	36	84	620
18MCN	M18	27	41	126	770
20MCN	M20	30	45	172	840
22MCN	M22	32	48	200	1,070
24MCN	M24	36	57	317	1,460

ヘビーナット

HEAVY NUT

- 材質 S45C
- 熱処理 焼入 HRC23~31
- 仕上 黒染




品番	A	B	C	質量 (g)	メーカー希望小売価格
	ねじ径				
10MHN	M10	17	10	14	220
12MHN	M12	19	12	19	260
14MHN	M14	22	14	30	280
16MHN	M16	24	15	36	360
18MHN	M18	27	18	55	420
20MHN	M20	30	20	74	490
22MHN	M22	32	22	89	580
24MHN	M24	36	24	131	740

六角ナット

HX. NUT

- 材質 S45C
- 熱処理 焼入 HRC23~31
- 仕上 黒染



品番	A	B	C	質量 (g)	メーカー希望小売価格
	ねじ径				
FTU 8	M 8	13	6.5	5	130
FTU 10	M10	17	8	10	160
FTU 12	M12	19	10	16	160
FTU 14	M14	22	11	23	160
FTU 16	M16	24	13	30	300
FTU 18	M18	27	15	46	360
FTU 20	M20	30	16	58	450
FTU 22	M22	32	18	74	590
FTU 24	M24	36	19	100	810