


## SB-A-(E)- • SBT-A- SUPER CARBIDE BUR



Shank diameter φ3mm (All carbide) Long Shank

Shape	Item No. (W. cut)	Size (mm)	
		L1	D
	SB1A0175	6	1.5
	SB1A0275	11	2.5
	SB1A0375	14	3
	SB1A01E75	14	3
	SB2A0275	14	3
	SB3A0175	12.7	3
	SB4A0375	12.7	3
	SB5A0375	11	3 <sup>14</sup>
	SB6A0175	5.5	3
	SB7A0175	12.7	3 <sup>8</sup>
	SB8A0275	2.5	3
	SB51A0175	6.3	3



Shank diameter φ3mm (All carbide) Long Shank

Shape	Item No. (W. cut)	Size (mm)	
		L1	D
	SB1A01100	6	1.5
	SB1A02100	11	2.5
	SB1A03100	14	3
	SB1A01E100	14	3
	SB2A02100	14	3
	SB3A01100	12.7	3
	SB4A03100	12.7	3
	SB5A03100	11	3 <sup>14</sup>
	SB6A01100	5.5	3
	SB7A01100	12.7	3 <sup>8</sup>
	SB8A02100	2.5	3
	SB51A01100	6.3	3

⚠ Lower the rotation speed.

Shank dia. φ3mm Titanium Coating Type (All carbide)

► **Feature** • The titanium (TiN) coating treatment provides high surface hardness, longer bur life and better cut-chip removal.



Shape	Item No. (W. cut)	Size (mm)		
		L	L1	D
	SBT1A01	38	6	1.5
	SBT1A02	38	11	2.5
	SBT1A03	38	14	3
	SBT2A01	38	11	2.5
	SBT2A02	38	14	3
	SBT3A01	38	12.7	3
	SBT4A01	38	9.5	3

Shape	Item No. (W. cut)	Size (mm)		
		L	L1	D
	SBT4A03	38	12.7	3
	SBT5A01	38	16	3 <sup>7</sup>
	SBT5A03	38	11	3 <sup>14</sup>
	SBT6A01	38	5.5	3
	SBT7A01	38	12.7	3 <sup>8</sup>
	SBT8A01	38	2.3	2.5
	SBT8A02	38	2.5	3

## SB3SH • SB3S SUPER CARBIDE BUR SET

► **Accessories** • Plastic case as standard acc.

Shank diameter φ3mm (W. cut) 5pcs-set

Set item No.	Set details
<b>SB3SH</b>	SB1A03·SB2A02·SB3A01·SB5A01·SB8A02

Shank diameter φ3mm (W. cut) 10pcs-set

Set item No.	Set details
<b>SB3S</b>	SB1A01·SB1A03·SB2A01·SB2A02·SB3A01·SB4A01·SB5A01·SB5A03·SB7A01·SB8A02

