


NCL Type (Simplex, Thread Connection)



NOMINAL SIZE		A	B	H	K	L ₁	L ₂	L	M	N	S
15A	1/2B	1/2	1/2	25	92	40	140	160	95	50	12
20A	3/4B	3/4	3/4	25	92	45	145	165	100	50	12
25A	1B	1	1	30	104	50	165	190	110	60	12
32A	1 1/4B	1 1/4	1 1/4	35	119	53	180	208	113	65	12
40A	1 1/2B	1 1/2	1 1/2	40	144	60	215	245	140	80	15
50A	2B	2	2	50	166	60	229	270	145	90	15
65A	2 1/2B	2 1/2	2 1/2	55	188	70	255	305	165	100	18
80A	3B	3	3	62	219	80	310	365	205	110	18

TYPE & SIZE: Example for placing order

Type → Size → Thread direction of Rotor: RH or LH


Example: NCL 25A RH

NCL

15A/20A/25A/32A
40A/50A/65A/80A

RH/LH

NCLF Type (Simplex, Flange Connection)



NOMINAL SIZE		B	H	K	L ₁	L ₂	L	M	N	S	FLANGE DIMENSIONS						
											A ₁	B ₁	C ₁	D ₁	E	F	BOLT
15A	1/2B	1/2	25	92	52	152	172	106	50	12	14	25	54	74	12	9	4-M10
20A	3/4B	3/4	25	92	45	145	165	100	50	12	17	26	54	74	12	8	4-M10
25A	1B	1	30	104	50	165	190	110	60	12	22	34	60	80	12	8	4-M10
32A	1 1/4B	1 1/4	35	119	53	180	208	113	65	12	30	42	75	96	14	10	4-M10
40A	1 1/2B	1 1/2	40	144	60	215	245	140	80	15	35	48	75	96	14	10	4-M10
50A	2B	2	50	166	60	229	270	145	90	15	48	60	95	120	14	12	4-M12
65A	2 1/2B	2 1/2	55	188	70	255	305	165	100	18	60	75	110	136	16	16	4-M12
80A	3B	3	62	219	80	310	365	205	110	18	72	90	125	154	20	22	6-M12

TYPE & SIZE: Example for placing order

Type → Size

Example: NCLF 25A

NCLF

15A/20A/25A/32A
40A/50A/65A/80A

- * The flange connection type is supplied with a copper gasket (to be attached on the shaft end), along with a stud bolt, nut and washer set.
- * When you place an order for the flange connection type, it is not necessary to specify the direction of the thread.
- * Since NC series has a split ring on the flange, be sure to use a gasket at the end of Rotor.