

MEASURING TAPES




G-PLUS™



GP-25BW

- The Hyper-Acry-Coat protective blade coating is non-reflective and provides superior scale readability
- Tempered steel Ultra-Hard End Hooks with 4-rivet attachment ensures consistently accurate inside and outside measurements
- Thick elastomer case armor extends around the body of the tape measure to protect end hooks and work surfaces



| ITEM CODE |  |  |  | CASE | MASTER CARTON | UPC | |
|-----------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|---------------|-----------------|-----------------|
| GP-16BW | 1 in (25 mm) | 16 ft | 7.87 ft / 2.4 m | 4 | 40 | 0-49296-02858-9 | |
| GP-25BW | | 25 ft | | | | 12.5 ft / 3.8 m | 0-49296-02859-6 |
| GP-30BW | | 30 ft | | | | | 0-49296-02860-2 |




G-SERIES™



G-25BW

- Shock-resistant, armored case
- The Hyper-Acry-Coat protective blade coating is non-reflective and provides superior scale readability
- Triple-riveted end hooks
- Cushioned end hook returns



| ITEM CODE |  |  |  | CASE | MASTER CARTON | UPC | |
|-------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------|---------------|-----------------|-----------------|
| G-6BW | 1 in (25 mm) | 6 ft | 4 ft / 1.2 m | 6 | 30 (5 sets) | 0-49296-02681-3 | |
| G-16BW | | 16 ft | 7.87 ft / 2.4 m | | | 12.5 ft / 3.8 m | 0-49296-02481-9 |
| G-25BW | | 25 ft | | | | | 0-49296-02459-8 |
| G-30BW | | 30 ft | | | | | 0-49296-02527-4 |
| G-5.5MBW | | 5.5 m | | | | | 0-49296-02985-2 |
| G-7.5MBW | | 7.5 m | | | | | 0-49296-02986-9 |
| G-16/5MBW | | 16 ft / 5 m | | | | | 0-49296-02918-0 |
| G-25/7.5MBW | | 25 ft / 7.5 m | | | | | 0-49296-02460-4 |
| G-33/10MBW | | 33 ft / 10 m | | | | | 0-49296-02919-7 |