


外觀寸法図

■製品のCADデータはホームページよりダウンロード可能です。



■ IP (防水保護等級) はサイズにより異なります。  
■ 自重は成形条件により5%内外の変動があります。

型番・寸法・標準価格

型番	W	D	H	a	b	c	d	e	f	g	h	i	j	k	l	IP	自重 (g)	標準価格
ALC 8-5-3	75	50	33	12	34	-	61	42.5	45.5	56	26	45	67	19	41	IP67	145	2,990
ALC10-5-3	100	50	33	12	34	-	86	67.5	45.5	81	26	70	92	19	41	IP67	175	3,910
ALC10-7-5	100	70	50	44	54	47	84	62.5	62.5	76	42	66	91	21.5	61	IP67	340	4,740
ALC12-9-6	120	90	60	62	40	64	102	79.5	81.5	96	52	82	107	20	76	IP67	560	5,280
ALC14-7-5	140	70	50	44	54	87	124	102.5	62.5	116	42	106	131	21.5	61	IP67	430	5,800
ALC14-11-6	140	110	60	82	60	84	122	99.5	101.5	116	52	102	127	40	96	IP67	685	7,750
ALC16-9-6	160	90	60	62	40	104	142	119.5	81.5	136	52	122	147	20	76	IP67	660	6,300
ALC16-13-7	160	130	70	102	80	104	142	119.5	121.5	136	62	122	147	60	117	IP67	890	9,490
ALC18-7-5	180	70	50	44	54	127	164	142.5	62.5	156	42	146	171	21.5	61	IP67	510	6,790
ALC18-15-6	180	150	60	122	100	124	162	139.5	141.5	156	52	142	170	80	140	IP67	1,000	9,900
ALC18-15-9	180	150	90	122	100	124	162	139.5	141.5	156	82	142	170	80	140	IP67	1,200	10,300
ALC20-11-6	200	110	60	82	60	144	182	159.5	101.5	176	52	162	186	40	96	IP67	860	8,410
ALC20-17-6	200	170	60	142	120	144	182	159.5	161.5	176	52	162	186	100	156	IP67	1,160	10,760
ALC20-17-9	200	170	90	142	120	144	182	159.5	161.5	176	82	162	186	100	156	IP67	1,380	11,390
ALC22-13-7	220	130	70	102	80	164	202	179.5	121.5	196	62	182	207	60	117	IP67	1,105	10,550
ALC23-20-12	230	200	120	172	144	174	212	189.5	191.5	206	112	192	220	123	189	IP65	2,050	23,630
ALC25-9-6	250	90	60	62	40	194	232	209.5	81.5	226	52	212	240	19	79	IP65	905	9,530
ALC26-15-6	260	150	60	122	100	204	242	219.5	141.5	236	52	222	250	80	138	IP65	1,240	10,550
ALC26-15-9	260	150	90	122	100	204	242	219.5	141.5	236	82	222	250	80	138	IP65	1,530	10,970
ALC28-17-6	280	170	60	142	120	224	262	239.5	161	256	52	242	270	100	159	IP65	1,470	12,040
ALC28-17-9	280	170	90	142	120	224	262	239.5	161	256	82	242	270	100	159	IP65	1,770	12,470
NEW ALC28-25-12	280	250	120	220	194	224	262	240	242	250	110	241	267	172	237	IP65	2,990	30,060
ALC33-20-12	330	200	120	172	144	274	312	289.5	191.5	306	112	292	320	123	189	IP65	2,600	28,990
NEW ALC33-30-12	330	300	120	270	244	274	312	290	292	300	110	291	318	222	288	IP65	3,890	38,390
NEW ALC38-25-12	380	250	120	220	194	324	362	340	242	350	110	341	367	172	236	IP65	3,700	31,980
NEW ALC43-30-12	430	300	120	270	244	374	412	390	292	400	109.5	390	417	220	287	IP65	4,700	49,800