


TACインサート ネガ

三角形穴つき

60°  ネガ

TN





TNMA 16 04 04

切れ刃長 (l) 厚さ (s) コーナ半径 (r_e)

TN 	1103 	1603 	1604 	2204
φd1 (mm)	2.26	3.81	3.81	5.16

TAC
インサート

- C
- D
- S
- T
- W
- V
- Y
- R
- K
- H

用途	ブレーカ記号 外観 (ブレーカ断面図)	f - a _p	形番	材種										適合バイト (掲載頁)							
				コーティング						サーメット		超硬			セラミック						
				T9115	T9125	T6120	T6130	T5105	T5115	T5125	GH110	GT720	NS520		NS530	TH03	TH10	FX105	LX21	LX11	
仕上げ 中切削	- (M)		TNMA160404																外径用TACバイト (4-22 ~, 4-86)		
			TNMA160408																		
			TNMA160412																		内径用TACバイト (5-36 ~)
			TNMA160416																		
			TNMA160420																		Jシリーズ (8-20)
			TNMA220404																		
			TNMA220408																		ツーリングシステム (12-70 ~)
			TNMA220412																		
	TNMA220416																				
	- (G)		TNGA110304																	外径用TACバイト (4-22 ~, 4-86)	
			TNGA110308																		
			TNGA160304																		内径用TACバイト (5-36 ~)
			TNGA160308																		
			TNGA160404																		Jシリーズ (8-20)
			TNGA160408																		
			TNGA160412																		ツーリングシステム (12-70 ~)
TNGA160416																					
TNGA220408																					

製品在庫 ●: 在庫形番 ▲: 将来新製品と置き換わる形番です