


FCH dimensions

• CAD data is downloadable from our website.



Color Type

Color code	Corner	Frame	Panel	Handle
GS	Light gray	Silver	Silver	Silver
BB	Black	Black	Black	Black

• Please suffix color code at the end of part number □□ when ordering FCH series.

Part no. / Dimensions

Part no.	H	W	D	a	Weight(kg)
FCH8-20-15□□	75.4	200	150	106.5	0.65
FCH8-20-20□□	75.4	200	200	106.5	0.79
FCH8-25-15□□	75.4	250	150	106.5	0.77
FCH8-25-20□□	75.4	250	200	106.5	0.93
FCH8-25-25□□	75.4	250	250	106.5	1.10
FCH8-30-20□□	75.4	300	200	126.5	1.07
FCH8-30-25□□	75.4	300	250	126.5	1.26
FCH8-30-30□□	75.4	300	300	126.5	1.45
FCH8-35-20□□	75.4	350	200	126.5	1.22
FCH8-35-25□□	75.4	350	250	126.5	1.42
FCH8-35-30□□	75.4	350	300	126.5	1.54
FCH8-40-25□□	75.4	400	250	126.5	1.49
FCH8-40-30□□	75.4	400	300	126.5	1.81
FCH8-40-40□□	75.4	400	400	126.5	2.27

Part no.	H	W	D	a	Weight(kg)
FCH10-30-20□□	100.4	300	200	126.5	1.19
FCH10-30-25□□	100.4	300	250	126.5	1.39
FCH10-30-30□□	100.4	300	300	126.5	1.60
FCH10-35-20□□	100.4	350	200	126.5	1.35
FCH10-35-25□□	100.4	350	250	126.5	1.57
FCH10-35-30□□	100.4	350	300	126.5	1.80
FCH10-40-25□□	100.4	400	250	126.5	1.75
FCH10-40-30□□	100.4	400	300	126.5	1.99
FCH10-40-40□□	100.4	400	400	126.5	2.48