


# Live Centers

The number next to the logo mark indicates items in stock for each brand.



Stock 38,650 Items



## "Half Center" (with carbide tip)



- Features**
- It is cut so that the tip of the lathe center does not get in contact with the work piece.
- Use**
- Prevents center run-out.
- Materials**
- Carbon Steel for Mechanical Structures (S45C)
  - A quenching polished item.
  - Carbide tip is JIS B 4104 applicable product
- Origin**
- Japan



THSP-2-840



Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shank	Total Length (mm)	Tip Diameter (mm)	Half length (mm)	End face distance (mm)	SPQ (piece)	Weight (kg)
491-9912	THSP-1-610	¥41,750	¥45,100	MT1	100	6	40	1.0	1	0.15
330-3918	THSP-2-820	¥30,798	¥33,270	MT2	125	8	50	2.0	1	0.20
330-3900	THSP-2-840	¥27,374	¥29,570	MT2	125	8	50	4.0	1	0.20
330-3934	THSP-3-1025	¥35,640	¥38,500	MT3	155	10	60	2.5	1	0.40
330-3926	THSP-3-1050	¥31,937	¥34,500	MT3	155	10	60	5.0	1	0.45
330-3951	THSP-4-1435	¥42,768	¥46,200	MT4	195	14	70	3.5	1	0.90
330-3942	THSP-4-1470	¥39,917	¥43,120	MT4	195	14	70	7.0	1	0.95
491-9921	THSP-4-1410	¥56,006	¥60,500	MT4	195	14	70	1.0	1	1.35
491-9939	THSP-4-1420	¥56,006	¥60,500	MT4	195	14	70	2.0	1	1.85
330-3977	THSP-5-1845	¥75,279	¥81,320	MT5	250	18	90	4.5	1	2.30
330-3969	THSP-5-1890	¥68,429	¥73,920	MT5	250	18	90	9.0	1	2.45

Contact us:0120-509-849 <http://www.orange-book.com/>




Stock 38,650 Items

## Lathe Center



- Use**
- Prevent vibration of workpieces.
- Materials**
- Carbon Steel for Mechanical Structures (SUJ-2)
  - A quenching polished item.
- Origin**
- Japan



### All steel solid type

Features •All steel is solid.

Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shank	Total Length (mm)	Tip Diameter (mm)	SPQ (piece)	Weight (kg)
230-6018	TRS-1	¥3,406	¥3,680	MT1	82	-	1	0.06
230-6034	TRS-2	¥3,813	¥4,120	MT2	100	-	1	0.16
230-6051	TRS-3	¥4,554	¥4,920	MT3	125	-	1	0.36
230-6077	TRS-4	¥6,425	¥6,940	MT4	155	-	1	0.74
230-6093	TRS-5	¥16,968	¥18,330	MT5	200	-	1	1.90
329-0395	TRS-6	¥39,917	¥43,120	MT6	270	-	1	5.20

### With Carbide Tip

Features •With a carbide tip.

Materials •Carbon Steel for Mechanical Structures (S45C)

(Price revision date: Jan, 2016)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shank	Total Length (mm)	Tip Diameter (mm)	SPQ (piece)	Weight (kg)
230-6026	TRSP-1	¥5,943	¥6,420	MT1	82	6	1	0.06
329-0301	TRSP-1-8	¥13,118	¥14,170	MT1	82	8	1	0.06
329-0310	TRSP-1-10	¥15,969	¥17,250	MT1	82	10	1	0.06
329-0328	TRSP-1-12	¥24,522	¥26,490	MT1	82	12	1	0.06
230-6042	TRSP-2	¥7,100	¥7,670	MT2	100	8	1	0.16
329-0336	TRSP-2-10	¥15,969	¥17,250	MT2	100	10	1	0.16
329-0344	TRSP-2-14	¥21,671	¥23,410	MT2	100	14	1	0.16
329-0352	TRSP-2-18	¥38,778	¥41,890	MT2	100	18	1	0.16
230-6069	TRSP-3	¥9,294	¥10,040	MT3	125	10	1	0.36
329-0361	TRSP-3-14	¥22,819	¥24,650	MT3	125	14	1	0.36
329-0379	TRSP-3-18	¥36,501	¥39,430	MT3	125	18	1	0.36
329-0387	TRSP-3-24	¥53,608	¥57,910	MT3	125	24	1	0.36
230-6085	TRSP-4	¥12,340	¥13,330	MT4	155	14	1	0.74
329-0263	TRSP-4-18	¥39,917	¥43,120	MT4	155	18	1	0.74
329-0271	TRSP-4-32	¥79,834	¥86,240	MT4	155	32	1	0.74
230-6107	TRSP-5	¥25,910	¥27,990	MT5	200	18	1	1.90
329-0280	TRSP-5-30	¥79,834	¥86,240	MT5	200	30	1	1.90
329-0298	TRSP-5-45	¥199,584	¥215,600	MT5	200	45	1	1.90
329-0441	TRSP-6	¥79,834	¥86,240	MT6	270	30	1	5.20

### Long Type/With Carbide Tip

Features •By lengthening the lathe center, the distance between the work-piece and tailstock becomes wider and work efficiency improves.

Materials •Carbon Steel for Mechanical Structures (S45C)

(Price revision date: Jan, 2016)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shank	Total Length (mm)	Tip Diameter (mm)	SPQ (piece)	Weight (kg)
329-0409	TRSP-L-2	¥22,819	¥24,650	MT2	140	8	1	0.25
329-0417	TRSP-L-3	¥27,374	¥29,570	MT3	160	10	1	0.50
329-0425	TRSP-L-4	¥31,937	¥34,500	MT4	200	14	1	1.00
329-0433	TRSP-L-5	¥57,034	¥61,610	MT5	245	18	1	2.40

Contact us:0120-509-849 <http://www.orange-book.com/>