

Prices displayed include 8% tax.


TRUSCO Stock 38,650 Items

## "E Type Hole Saw"

Regrinding OK



- Features**
- Optimum for drilling iron plate with safety design that engagement will not occur.
  - Ideal for drilling of iron plate, zinc iron plate, tinplate, etc.
  - Only for electric drill.
- Materials**
- Blade Part: High Speed Steel (SKH51)
  - Center Drills: TE10.5 to TE100 (high speed steel SKH51) TE105 to TE150 (cobalt high speed steel SKH59)
- Origin**
- Japan



Iron Plate 1.6mm

TE Series



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Throat Height (mm)	Shank Diameter (mm)	Blade Thickness (mm)	SPQ (piece)	Weight (g)	Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Throat Height (mm)	Shank Diameter (mm)	Blade Thickness (mm)	SPQ (piece)	Weight (g)
352-1613	TE10.5	¥2,981	¥3,680	10.5	8	10	1.5	12	60	352-1656	TE52	¥6,035	¥7,450	52	8	10	2.4	6	240
352-1575	TE12	¥1,636	¥2,020	12.0	8	10	1.5	12	60	352-2024	TE53	¥6,035	¥7,450	53	8	10	2.4	6	260
352-1541	TE13	¥1,636	¥2,020	13.0	8	10	1.6	12	60	352-2903	TE54	¥6,035	¥7,450	54	8	10	2.4	6	260
352-1524	TE14	¥1,636	¥2,020	14.0	8	10	1.7	12	60	352-2008	TE55	¥6,035	¥7,450	55	8	10	2.4	6	260
352-1516	TE15	¥1,636	¥2,020	15.0	8	10	1.9	12	60	352-2644	TE56	¥6,408	¥7,910	56	8	10	2.4	1	290
352-1508	TE16	¥1,774	¥2,190	16.0	8	10	1.9	12	60	352-2652	TE57	¥6,408	¥7,910	57	8	10	2.4	1	300
352-1494	TE17	¥1,774	¥2,190	17.0	8	10	1.9	12	60	352-2661	TE58	¥6,408	¥7,910	58	8	10	2.4	1	300
352-1486	TE18	¥1,774	¥2,190	18.0	8	10	1.9	12	70	352-2679	TE59	¥6,408	¥7,910	59	8	10	2.4	1	310
352-1478	TE19	¥1,774	¥2,190	19.0	8	10	1.9	12	70	352-2768	TE60	¥6,408	¥7,910	60	8	10	2.4	1	310
352-1460	TE20	¥1,912	¥2,360	20.0	8	10	2.0	12	70	352-2695	TE61	¥6,408	¥7,910	61	8	12	2.4	1	320
352-1788	TE21	¥1,912	¥2,360	21.0	8	10	2.0	12	70	352-2636	TE62	¥6,408	¥7,910	62	8	12	2.4	1	330
352-1583	TE22	¥1,912	¥2,360	22.0	8	10	2.0	12	80	352-2717	TE63	¥6,408	¥7,910	63	8	12	2.4	1	340
352-1630	TE23	¥1,912	¥2,360	23.0	8	10	2.0	12	80	352-2725	TE64	¥6,408	¥7,910	64	8	12	2.4	1	350
352-1800	TE24	¥1,912	¥2,360	24.0	8	10	2.0	12	80	352-2741	TE65	¥6,408	¥7,910	65	8	12	2.4	1	350
352-1818	TE25	¥2,203	¥2,720	25.0	8	10	2.1	12	90	352-1991	TE66	¥7,484	¥9,240	66	8	12	2.4	1	360
352-1826	TE26	¥2,203	¥2,720	26.0	8	10	2.1	12	100	352-1982	TE67	¥7,484	¥9,240	67	8	12	2.4	1	370
352-1834	TE27	¥2,203	¥2,720	27.0	8	10	2.1	12	100	352-1974	TE68	¥7,484	¥9,240	68	8	12	2.4	1	370
352-1842	TE28	¥2,341	¥2,890	28.0	8	10	2.1	12	100	352-1966	TE69	¥7,484	¥9,240	69	8	12	2.4	1	370
352-1931	TE29	¥2,341	¥2,890	29.0	8	10	2.1	12	100	352-1958	TE70	¥7,484	¥9,240	70	8	12	2.4	1	390
352-1869	TE30	¥2,341	¥2,890	30.0	8	10	2.2	12	110	352-1940	TE71	¥7,484	¥9,240	71	8	12	2.4	1	400
352-1796	TE31	¥2,341	¥2,890	31.0	8	10	2.2	12	110	352-2750	TE72	¥7,484	¥9,240	72	8	12	2.4	1	410
352-1885	TE32	¥2,341	¥2,890	32.0	8	10	2.2	12	120	352-2521	TE73	¥11,421	¥14,100	73	8	12	2.4	1	420
352-1893	TE33	¥3,135	¥3,870	33.0	8	10	2.2	12	140	352-2709	TE74	¥11,421	¥14,100	74	8	12	2.4	1	420
352-1907	TE34	¥3,135	¥3,870	34.0	8	10	2.2	12	140	352-2687	TE75	¥11,421	¥14,100	75	8	12	2.4	1	440
352-1915	TE35	¥3,135	¥3,870	35.0	8	10	2.2	12	150	352-2610	TE76	¥11,421	¥14,100	76	8	12	2.4	1	440
352-1923	TE36	¥3,135	¥3,870	36.0	8	10	2.2	6	150	352-2601	TE77	¥11,421	¥14,100	77	8	12	2.4	1	440
352-1648	TE37	¥4,617	¥5,700	37.0	8	10	2.2	6	150	352-2598	TE78	¥11,421	¥14,100	78	8	12	2.4	1	460
352-1877	TE38	¥4,617	¥5,700	38.0	8	10	2.2	6	160	352-2580	TE79	¥11,421	¥14,100	79	8	12	2.4	1	470
352-1851	TE39	¥4,617	¥5,700	39.0	8	10	2.2	6	160	352-2571	TE80	¥11,421	¥14,100	80	8	12	2.4	1	480
352-1770	TE40	¥4,617	¥5,700	40.0	8	10	2.3	6	170	352-2563	TE85	¥15,633	¥19,300	85	8	12	2.4	1	500
352-1761	TE41	¥4,617	¥5,700	41.0	8	10	2.3	6	180	352-2547	TE90	¥15,633	¥19,300	90	8	12	2.4	1	560
352-1753	TE42	¥4,617	¥5,700	42.0	8	10	2.3	6	180	352-2539	TE95	¥15,633	¥19,300	95	8	12	2.4	1	600
352-1745	TE43	¥5,330	¥6,580	43.0	8	10	2.3	6	190	352-1621	TE100	¥17,764	¥21,930	100	8	12	2.4	1	660
352-1737	TE44	¥5,330	¥6,580	44.0	8	10	2.3	6	190	352-1451	TE105	¥28,423	¥35,090	105	8	13	2.4	1	940
352-1729	TE45	¥5,330	¥6,580	45.0	8	10	2.3	6	200	352-1605	TE110	¥31,979	¥39,480	110	8	13	2.4	1	1010
352-1711	TE46	¥5,330	¥6,580	46.0	8	10	2.3	6	200	352-1591	TE115	¥31,979	¥39,480	115	8	13	2.4	1	1070
352-1702	TE47	¥6,035	¥7,450	47.0	8	10	2.3	6	230	352-1567	TE120	¥31,979	¥39,480	120	8	13	2.4	1	1150
352-1699	TE48	¥6,035	¥7,450	48.0	8	10	2.3	6	230	352-1559	TE125	¥39,083	¥48,250	125	8	13	2.4	1	1200
352-1681	TE49	¥6,035	¥7,450	49.0	8	10	2.3	6	240	352-1532	TE130	¥42,638	¥52,640	130	8	13	2.4	1	1270
352-1672	TE50	¥6,035	¥7,450	50.0	8	10	2.4	6	240	352-3080	TE140	¥53,298	¥65,800	140	8	13	2.4	1	1420
352-1664	TE51	¥6,035	¥7,450	51.0	8	10	2.4	6	240	352-3098	TE150	¥60,345	¥74,500	150	8	13	2.4	1	1570



TE645 (center drill)

Center Drill

Materials • TE645 (high speed steel SKH51) TE850 (cobalt high speed steel SKH59)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Cutting Diameter (mm)	Total Length (mm)	Compatible Model	SPQ (piece)	Weight (g)
352-2733	TE645	¥495	¥610	6	45	TE10.5 to 100	10	10
352-2555	TE850	¥802	¥990	8	60	TE105 to 150	10	20

Contact us: 0120-509-849 <http://www.orange-book.com/>

Drills

Coated Carbide Drills

Carbide Drills

High Speed Steel Coated Drills

High Speed Steel Drills

Thin Shaft Drills

Spot Cutters

Taper Shank Drills

Hex Shank Ironsmith Drills

Drill Sets

Drill Cases

Step Drills

Cutters for Magnetic Cutting Unit

Hole Saws

Core Drills

Concrete Drills

Drills

Bits, Cutters for Wood

For other cutting tools, see p. 1-805 to 1006