

For Die Handle, see p. 1-424 to 425

The number next to the logo mark indicates items in stock for each brand.

OSG Stock 8,256 Items

Taper Pipe Die (PT thread)



TPD-PT Series

- Features •Solid-type die.
Use •Work Material: Low Carbon Steel
•For external thread machining.
Specs •Machining Thread: Taper Thread for Pipe PT
Materials •Alloy Tool Steel (SKS)
Origin •Japan

Order Unit: 1 Piece

SPQ: 10 Pieces
OSG CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)
634-2213	TPD-38XPT1/4-19	¥ 7,628	¥ 9,430	1/4	19	38	11
634-2230	TPD-38XPT3/8-19	¥ 7,628	¥ 9,430	3/8	19	38	11
634-2256	TPD-50XPT1/4-19	¥ 12,636	¥ 15,600	1/4	19	50	16
634-2264	TPD-50XPT3/8-19	¥ 12,636	¥ 15,600	3/8	19	50	18
634-2248	TPD-50XPT1/2-14	¥ 12,636	¥ 15,600	1/2	14	50	22

Contact us:0120-41-5981 <http://www.osg.co.jp/>

ISHIHASHI Stock 1,202 Items

Adjustable Taper Pipe Die (PT thread)



IS-RD-38-PT014

- Features •Internal thread tool that has a hole to release chip.
•Comes with adjustable screw.
Use •For external thread machining.
•Work Material: Low Carbon Steel
Specs •Machining Thread: PT Thread for Pipe
Materials •Tungsten steel (SKS2) Origin •Japan

Order Unit: 1 Piece

ISHIHASHI SEIKO

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)	SPQ (piece)
484-7911	IS-RD-38-PT018	¥ 7,413	¥ 9,610	PT1/8	28	38	13	10
484-7903	IS-RD-38-PT014	¥ 7,413	¥ 9,610	PT1/4	19	38	13	10
484-8128	IS-RD-50-PT038	¥ 12,705	¥ 16,470	PT3/8	19	50	16	10
484-8101	IS-RD-50-PT012	¥ 12,705	¥ 16,470	PT1/2	14	50	16	10
484-8110	IS-RD-50-PT034	¥ 12,705	¥ 16,470	PT3/4	14	50	16	10
484-8144	IS-RD-63-PT1	¥ 32,076	¥ 41,580	PT1	11	63	20	1

Contact us:072-982-0123


TRUSCO Stock 38,650 Items

Round Adjustable Parallel Pipe Die (PS thread)



TKD-38PS1/8-28

- Features •Adjustable screw allows you to adjust the dimension.
•Can also be used when repairing ridge.
Use •Work Material: Iron, Light Metal.
•For external thread machining.
Specs •Machining Thread: Parallel Thread for Pipe PS
Materials •Low-Alloy Steel (SKS2) Origin •Japan



Warning
•Cannot be used for stainless steel screws.

SPQ: 1 Piece

Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)
480-6506	TKD-38PS1/8-28	¥ 5,176	¥ 6,390	1/8	28	38	14
480-6492	TKD-38PS1/4-19	¥ 5,176	¥ 6,390	1/4	19	38	14
480-6581	TKD-50PS3/8-19	¥ 6,901	¥ 8,520	3/8	19	50	16
480-6565	TKD-50PS1/2-14	¥ 6,901	¥ 8,520	1/2	14	50	16
480-6573	TKD-50PS3/4-14	¥ 6,901	¥ 8,520	3/4	14	50	16
480-6638	TKD-63PS1-11	¥ 19,967	¥ 24,650	1	11	63	19
858-7622	TKD-75PS11/2-11	¥ 38,718	¥ 47,800	1 1/2	11	75	25
858-7623	TKD-75PS11/4-11	¥ 38,718	¥ 47,800	1 1/4	11	75	25

Contact us:0120-509-849 <http://www.orange-book.com/>

OSG Stock 8,256 Items

Parallel Pipe Die (PS thread)



SPD-PS Series

- Features •Adjustable screw allows you to adjust the dimension.
Use •Work Material: Low Carbon Steel
•For external thread machining.
Specs •Machining Thread: Parallel Thread for Pipe PS
Materials •Alloy Tool Steel (SKS)
Origin •Japan

SPQ: 10 Pieces

OSG CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)
634-1161	SPD-38XPS1/8-28	¥ 5,076	¥ 6,270	1/8	28	38	13
634-1152	SPD-38XPS1/4-19	¥ 5,076	¥ 6,270	1/4	19	38	13
634-1179	SPD-38XPS3/8-19	¥ 5,076	¥ 6,270	3/8	19	38	13
634-1233	SPD-50XPS3/8-19	¥ 8,424	¥ 10,400	3/8	19	50	16
634-1217	SPD-50XPS1/2-14	¥ 8,424	¥ 10,400	1/2	14	50	16

Contact us:0120-41-5981 <http://www.osg.co.jp/>