

Plate Type/Threaded Type Dual Wheel Casters

Stock 265Items

2-753

Prices displayed include 8% tax.




Stock 42 Items

Plate Type Dual Wheel Caster (elastomer wheel)



- Features • Demonstrates a high turning capacity because of dual wheel.
 Specs • Plate Type
 Materials • Metal Fitting: Steel
 • Wheel: Elastomer
 Origin • Japan



F050

F050, F060

Flexible Specs • Flexible Type


Order Unit: 1 Piece

TOKAI CASTER

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Mounting Plate A x B (mm)	Mounting Pitch X x Y (mm)	Mounting Hole Diameter P (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)								
389-0473	F050	¥ 679	-	58.8	60	50	43.5	66.0	54	40	5.5	100	143
389-0481	F050F	¥ 679	-	58.8	60	50	43.5	66.0	60 x 50	46 x 35	6.5	100	169
389-0571	F060	¥ 872	-	78.4	80	60	46.0	76.0	54	40	5.5	100	172
389-0589	F060F	¥ 872	-	78.4	80	60	46.0	76.0	60 x 50	46 x 35	6.5	100	199
389-0678	F075	¥ 1,651	-	78.4	80	75	47.0	93.0	60 x 50	46 x 35	6.5	40	248
389-0759	F100	¥ 2,330	-	78.4	80	100	47.0	117.5	60 x 50	46 x 35	6.5	20	340
389-0830	F130	¥ 3,903	-	98.0	100	130	50.0	153.5	66 x 66	50 x 50	6.2	20	588



F050F



F050F, F060F, F075, F100, F130


Flexible with stopper Specs • Flexible Type (with stopper)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Mounting Plate A x B (mm)	Mounting Pitch X x Y (mm)	Mounting Hole Diameter P (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)								
389-0554	F050S	¥ 802	-	58.8	60	50	43.5	66	54	40	5.5	100	152
389-0562	F050SF	¥ 802	-	58.8	60	50	43.5	66	60 x 50	46 x 35	6.5	100	179
389-0651	F060S	¥ 1,018	-	78.4	80	60	46.0	76	54	40	5.5	100	178
389-0660	F060SF	¥ 1,018	-	78.4	80	60	46.0	76	60 x 50	46 x 35	6.5	100	205



F050S



F050S, F060S

Flexible with double stopper Specs • Flexible Type (with double stopper)


• Simultaneously lock the turning part and the wheel

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Mounting Plate A x B (mm)	Mounting Pitch X x Y (mm)	Mounting Hole Diameter P (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)								
389-0741	F075WS	¥ 2,083	-	78.4	80	75	47	93.0	60 x 50	46 x 35	6.5	40	271
389-0821	F100WS	¥ 2,623	-	78.4	80	100	47	117.5	60 x 50	46 x 35	6.5	20	369
389-0881	F130WS	¥ 4,335	-	98.0	100	130	50	153.5	66 x 66	50 x 50	6.2	20	661



F050SF



F050SF, F060SF, F075WS, F100WS, F130WS

Contact us: 052-401-3302 <http://www.tokai-caster.co.jp/>



Stock 38,650 Items

Threaded Type Double Wheel Caster (nylon wheel)



- Features • A standard good for cheap and lightweight products.
 Specs • Threaded type
 Materials • Metal Fitting: Carbon Steel for Cold Forging (SWCH)
 • Metal Fitting Surface Treatment: Trivalent Chrome Plated Finishing
 • Main Body: Nylon
 • Wheel: Nylon
 Origin • Japan

Flexible Specs • Flexible Type


Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Shaft Length L (mm)	Screw T	Thread Pitch (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)								
765-8842	TDG-40-M8	¥ 213	¥ 230	29	30	40	42	51	15	M8	1.25	200	55
765-8834	TDG-40-M10	¥ 213	¥ 230	29	30	40	42	51	15	M10	1.50	200	58
765-8877	TDG-50-M8	¥ 296	¥ 320	39	40	50	48	63	15	M8	1.25	100	84
765-8851	TDG-50-M10	¥ 296	¥ 320	39	40	50	48	63	15	M10	1.50	100	87
765-8869	TDG-50-M12	¥ 296	¥ 320	39	40	50	48	63	15	M12	1.25	100	94



TDG-50-M8



Flexible with stopper Specs • Flexible Type (with stopper)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Shaft Length L (mm)	Screw T	Thread Pitch (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)								
765-8893	TDGS-40-M8	¥ 278	¥ 300	29	30	40	42	51	15	M8	1.25	200	59
765-8885	TDGS-40-M10	¥ 278	¥ 300	29	30	40	42	51	15	M10	1.50	200	62
765-8923	TDGS-50-M8	¥ 342	¥ 370	39	40	50	48	63	15	M8	1.25	100	90
765-8907	TDGS-50-M10	¥ 342	¥ 370	39	40	50	48	63	15	M10	1.50	100	93
765-8915	TDGS-50-M12	¥ 342	¥ 370	39	40	50	48	63	15	M12	1.25	100	100



TDGS-50-M8

Contact us: 0120-509-849 <http://www.orange-book.com/>

Casters

Plate Type Rubber Casters

Plate Type Urethane Casters

Plate Type Nylon Casters

Plate Type Resin Casters

Screwed Rubber Casters

Screwed Urethane Casters

Screwed Nylon Casters

Screwed Resin Casters

Nuts, Spanners

Stem Casters

Stainless Steel Casters

Angle Casters

Corner Casters

Dual Wheel Casters

Sound Reducing Casters

ESD-Safe Casters

Shock Absorbing Casters

Casters for Specific Environment

Pneumatic/No-Puncture Caster

Low Level Casters

Heavy-Duty Casters

Casting Casters

Stoppers

2-753