


Disc Papers (screw-in type)

Stock 1,281 Items

5-945

Prices displayed include 8% tax.

For Disc Grinders, see p. 5-209 to 226



Stock 38,650 Items

Disc Paper "GP Top[®] α" (directly threaded type)



- Features**
- Designed to be difficult to get clogging because it is a special mold.
 - Noise is less and can be used comfortably.
 - Can be installed with one touch (screw type). (only disc grinder)
- Use**
- Heavy grinding, metal polishing by disc grinder.
 - Remove welding bead.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
- Origin**
- Japan



GP100AL: 80
(aluminum for general metal)

Estimated Unit Price per Sheet
¥446



GP100AL-60-100P
(100 sheets, aluminum for general metal)

Estimated Unit Price per Sheet
¥430



GP100ALZ: 80
(zirconia for stainless steel, difficult-to-cut material)

Estimated Unit Price per Sheet
¥446




GP100ALC-80
(ceramic for difficult-to-cut material)

Estimated Unit Price per Sheet
¥794

The geometric comparison blade of GP top[®] α and conventional GP Top[®]

achieves high grinding force even at 72 sheets. GP top[®] α reduces the number of sheet blades by 8 to lower the cost, on the other hand, increasing the blade length by 3mm to prevent lowering capacity (grinding force reduction) from conventional GP top[®] and suppressing clogging by block planting and improved grinding force.



Aluminum (for general metal) Use

• For polishing of general metal, wood.

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Screw Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
114-8931	GP100AL	40	¥4,455	¥5,500	40	100 x 19.5 x M10 (P1.5)	13600	72	10	10	800
114-8940	GP100AL	60	¥4,455	¥5,500	60	100 x 19.5 x M10 (P1.5)	13600	80	10	10	750
114-8958	GP100AL	80	¥4,455	¥5,500	80	100 x 19.5 x M10 (P1.5)	13600	80	10	10	700
114-8966	GP100AL	100	¥4,455	¥5,500	100	100 x 19.5 x M10 (P1.5)	13600	80	10	10	670
114-8974	GP100AL	120	¥4,455	¥5,500	120	100 x 19.5 x M10 (P1.5)	13600	80	10	10	640
114-8982	GP100AL	150	¥4,455	¥5,500	150	100 x 19.5 x M10 (P1.5)	13600	80	10	10	640
114-8991	GP100AL	180	¥4,455	¥5,500	180	100 x 19.5 x M10 (P1.5)	13600	80	10	10	640
114-9008	GP100AL	240	¥4,455	¥5,500	240	100 x 19.5 x M10 (P1.5)	13600	80	10	10	640
114-9016	GP100AL	320	¥4,455	¥5,500	320	100 x 19.5 x M10 (P1.5)	13600	80	10	10	640
114-9024	GP100AL	400	¥4,455	¥5,500	400	100 x 19.5 x M10 (P1.5)	13600	80	10	10	640

100 Sheets, Aluminum (for general metal)



Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Screw Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (kg/box)
829-1351	GP100AL-60-100P	¥42,930	¥53,000	60	100 x 19.5 x M10 (P1.5)	13600	80	100	1	7.5
829-1352	GP100AL-80-100P	¥42,930	¥53,000	80	100 x 19.5 x M10 (P1.5)	13600	80	100	1	7.2
829-1353	GP100AL-100-100P	¥42,930	¥53,000	100	100 x 19.5 x M10 (P1.5)	13600	80	100	1	8.3
829-1354	GP100AL-120-100P	¥42,930	¥53,000	120	100 x 19.5 x M10 (P1.5)	13600	80	100	1	7.8

Zirconia (for stainless steel/difficult-to-cut material)

Use • Demonstrate its effectiveness in high-hardness metal polishing such as stainless steel, difficult-to-cut materials.

Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Screw Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
114-9032	GP100ALZ	40	¥4,455	¥5,500	40	100 x 19.5 x M10 (P1.5)	13600	72	10	10	890
114-9041	GP100ALZ	60	¥4,455	¥5,500	60	100 x 19.5 x M10 (P1.5)	13600	80	10	10	830
114-9059	GP100ALZ	80	¥4,455	¥5,500	80	100 x 19.5 x M10 (P1.5)	13600	80	10	10	780
215-8001	GP100ALZ	100	¥4,455	¥5,500	100	100 x 19.5 x M10 (P1.5)	13600	80	10	10	750
215-8019	GP100ALZ	120	¥4,455	¥5,500	120	100 x 19.5 x M10 (P1.5)	13600	80	10	10	740

Ceramic (for difficult-to-cut material)

Features • Ceramic abrasive grains with high grinding force and high durability are implanted.
Use • Designed the type of difficult to get clogging because it is a special mold different from ordinary.
Use • For difficult-to-cut material such as stainless steel, titanium, nickel steel.

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Screw Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
384-1812	GP100ALC-40	¥7,938	¥9,800	40	100 x 19.5 x M10 (P1.5)	13600	72	10	10	1030
384-1821	GP100ALC-60	¥7,938	¥9,800	60	100 x 19.5 x M10 (P1.5)	13600	72	10	10	900
384-1839	GP100ALC-80	¥7,938	¥9,800	80	100 x 19.5 x M10 (P1.5)	13600	72	10	10	850
384-1847	GP100ALC-120	¥7,938	¥9,800	120	100 x 19.5 x M10 (P1.5)	13600	72	10	10	790

Contact us: 0120-509-849 <http://www.orange-book.com/>

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes