

Nylon Discs

For Disc Grinders, see p. 5-209 to 226

The number next to the logo mark indicates items in stock for each brand.

TRUSCO



Stock 38,650 Items

"New Nylon Disc"



TNND100-120
(outer diameter 95mm)
Outer Diameter 95mm
Estimated Unit Price per Piece
¥1,004

Video



Outer Diameter 125mm
Estimated Unit Price per Piece
¥1,426

- Features**
- Even without adjusting the rotation speed, there is no burning or clogging. (High rotation model)
 - Nylon abrasive, which is made by sticking intertwined nylon fiber with abrasive, is used.
 - Can polish without grinding the polishing materials too much.
- Use**
- Welding burn removal, curve surface of woodwork, R part sealer sanding, finishing before painting, satin finish, mirror surface pre-processing, paint removal.
- Origin**
- Japan

Outer Diameter 95mm Specs •Max Working Peripheral Velocity: 59.7m/s (3580m/min)
Accessories •Only φ95 adapter for 15mm hole 1 piece per box (sold separately item no.: GPTA-1P)

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Layers of Non-Woven Fabric (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
379-9760	TNND100-60	¥5,022	¥6,200	60	95 x 15 x 16	12000	27	5	20	385
379-9778	TNND100-120	¥5,022	¥6,200	120	95 x 15 x 16	12000	28	5	20	390
379-9786	TNND100-240	¥5,022	¥6,200	240	95 x 15 x 16	12000	28	5	20	370
379-9794	TNND100-320	¥5,022	¥6,200	320	95 x 15 x 16	12000	29	5	20	350
379-9808	TNND100-600	¥5,022	¥6,200	600	95 x 15 x 16	12000	30	5	20	330

Outer Diameter 125mm Specs •Max Working Peripheral Velocity: 58.9m/s (3533m/min)

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Layers of Non-Woven Fabric (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
379-9816	TNND125-60	¥7,128	¥8,800	60	125 x 15 x 16	9000	29	5	10	628
379-9824	TNND125-120	¥7,128	¥8,800	120	125 x 15 x 16	9000	35	5	10	550
379-9832	TNND125-240	¥7,128	¥8,800	240	125 x 15 x 16	9000	35	5	10	608
379-9841	TNND125-320	¥7,128	¥8,800	320	125 x 15 x 16	9000	35	5	10	608
379-9859	TNND125-600	¥7,128	¥8,800	600	125 x 15 x 16	9000	36	5	10	578

Outer Diameter 180mm Specs •Max Working Peripheral Velocity: 61.2m/s (3674m/min)

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Layers of Non-Woven Fabric (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
379-9867	TNND180-60	¥12,150	¥15,000	60	180 x 15 x 22	6500	45	5	5	1.37
379-9875	TNND180-120	¥12,150	¥15,000	120	180 x 15 x 22	6500	55	5	5	1.32
379-9883	TNND180-240	¥12,150	¥15,000	240	180 x 15 x 22	6500	55	5	5	1.29
379-9891	TNND180-320	¥12,150	¥15,000	320	180 x 15 x 22	6500	55	5	5	1.27
379-9905	TNND180-600	¥12,150	¥15,000	600	180 x 15 x 22	6500	58	5	5	1.23

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO



Stock 38,650 Items

"New Nylon Disc" (direct screw-in type)



TNND100AL-120
Estimated Unit Price per Piece
¥1,004

- Features**
- Can be installed with one touch (screw type).
 - Even without adjusting the rotation speed, there is no burning or clogging. (High rotation model)
 - Nylon abrasive, which is made by sticking intertwined nylon fiber with abrasive, is used.
 - Can polish without grinding the polishing materials too much.
- Use**
- Welding burn removal, curve surface of woodwork, R part sealer sanding, finishing before painting, satin finish, mirror surface pre-processing, paint removal.
- Specs**
- Max Working Peripheral Velocity: 59.7m/s (3580m/min)
- Origin**
- Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Layers of Non-Woven Fabric (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
379-9913	TNND100AL-60	¥5,022	¥6,200	60	95 x 15 x M10 (P1.5)	12000	27	5	20	467
379-9921	TNND100AL-120	¥5,022	¥6,200	120	95 x 15 x M10 (P1.5)	12000	28	5	20	432
379-9930	TNND100AL-240	¥5,022	¥6,200	240	95 x 15 x M10 (P1.5)	12000	28	5	20	422
379-9948	TNND100AL-320	¥5,022	¥6,200	320	95 x 15 x M10 (P1.5)	12000	29	5	20	392
379-9956	TNND100AL-600	¥5,022	¥6,200	600	95 x 15 x M10 (P1.5)	12000	30	5	20	372

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO



Stock 38,650 Items

"GP Nylon Mix Disc" (directly threaded type)



GPNM-100AL:240
Estimated Unit Price per Piece
¥1,094

- Features**
- By mixing polishing non-woven fabric and polishing cloth, the fiber plays the role of cushions and clogging is hard to occur so that deep scratches do not enter like paper and finish only the surface.
 - Excellent polishing force. A long life, flexible, rounded head polishing surface can be obtained, making it optimum for finishing the curved surface.
- Use**
- Oxide coating and rust removal, roughening before coating and laminate.
 - Cleaning before welding. •Removal of burn after welding of stainless etc.
 - From coarse mesh finish to fine finish of stainless steel, aluminum etc.
- Specs**
- Max Working Peripheral Velocity: 68m/s (4080m/min)
- Origin**
- Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Layers of Non-Woven Fabric (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
275-6129	GPNM-100AL	120	¥5,468	¥6,750	120	100 x 15 x M10 (P1.5)	13000	55	5	20	440
275-6137	GPNM-100AL	240	¥5,468	¥6,750	240	100 x 15 x M10 (P1.5)	13000	55	5	20	390
275-6145	GPNM-100AL	320	¥5,468	¥6,750	320	100 x 15 x M10 (P1.5)	13000	59	5	20	390
275-6153	GPNM-100AL	600	¥5,468	¥6,750	600	100 x 15 x M10 (P1.5)	13000	59	5	20	360

Contact us:0120-509-849 <http://www.orange-book.com/>

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes