

Disc Papers (double-sided design) / Disc Papers (mini type)

Stock 1,281 Items

5-951

Prices displayed include 8% tax.

For Disc Grinders, see p. 5-209 to 226

TRUSCO Stock 38,650 Items

"GP Multi Disc"



Com.eco Chemical Content Inspection Drawing SDS

- Features**
- Since the pad is small and has cushioning properties, there is no worry of deep grinding and it exhibits performance on the protruding surfaces and recessed surfaces of flat surfaces.
 - Economical as it can be used to the end.
 - Capable of polishing with the side surface.
 - Soft touch for less fatigue.
 - Professional abrasive which is planted one by one by hand and caulked.
- Use**
- For welding bead removal, paint removal, polishing before plating. Ideal for polishing of stainless steel, iron, alloys, wood, and plastic, etc.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
- Origin**
- Japan




GP100M (aluminum for general metal)

Estimated Unit Price per Sheet ¥1,134



GP100MZ (zirconia for heavy polishing)

Estimated Unit Price per Sheet ¥1,134



Aluminum (for general metal)

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
156-9198	GP100M	150	¥5,670	¥7,000	150	100 x 30 x 15	13600	5 x 18	5	20	510
156-9201	GP100M	180	¥5,670	¥7,000	180	100 x 30 x 15	13600	5 x 18	5	20	500
156-9210	GP100M	240	¥5,670	¥7,000	240	100 x 30 x 15	13600	5 x 18	5	20	490
156-9228	GP100M	320	¥5,670	¥7,000	320	100 x 30 x 15	13600	5 x 18	5	20	475
156-9236	GP100M	400	¥5,670	¥7,000	400	100 x 30 x 15	13600	5 x 18	5	20	440

Zirconia (for heavy polishing)

- Features**
- Has a good bite on the material being ground.
- Use**
- Especially ideal for grinding and polishing of stainless steel, etc.



Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
115-0936	GP100MZ	40	¥5,670	¥7,000	40	100 x 30 x 15	13600	3 x 18	5	20	560
115-0944	GP100MZ	60	¥5,670	¥7,000	60	100 x 30 x 15	13600	4 x 18	5	20	550
115-0952	GP100MZ	80	¥5,670	¥7,000	80	100 x 30 x 15	13600	4 x 18	5	20	525
115-0961	GP100MZ	100	¥5,670	¥7,000	100	100 x 30 x 15	13600	4 x 18	5	20	500
115-0979	GP100MZ	120	¥5,670	¥7,000	120	100 x 30 x 15	13600	4 x 18	5	20	480

Contact us: 0120-509-849 <http://www.orange-book.com/>

MIYUKI SANGYO Stock 93 Items

Disc Paper "ESPER MINI"



- Features**
- Has more than 10x the durability of disc paper and 10x the durability of offset whetstones.
 - Contact with the work being ground is soft, attraction is nice, and deep scratches are not created which makes the next step easier.
- Use**
- Burr removal for spot welding of automobiles and home electric appliances, etc.
 - Welding bead removal for ship building, iron frames, and bridges, etc.
 - Burr removal of metal.
 - Surface preparation and rust removal for plating and painting.
 - Polishing of woodwork plastic.
 - Chamfering.
- Specs**
- Max Working Peripheral Velocity: 60.7m/s (3642m/min)
 - **Outer Diameter: 58mm**
- Origin**
- Japan



MMEM58A-120 (aluminum for general metal)



MMEM58Z-80 (zirconia for stainless steel/difficult-to-cut material)

Aluminum (for general metal)

Order Unit: 5 Sheets

MIYUKI SANGYO

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Weight (g)
474-0262	MMEM58A-40	¥648*	¥800*	5	40	58 x 15 x 9.6	20000	48	22
474-0289	MMEM58A-60	¥648*	¥800*	5	60	58 x 15 x 9.6	20000	48	19
474-0297	MMEM58A-80	¥648*	¥800*	5	80	58 x 15 x 9.6	20000	48	17
474-0203	MMEM58A-100	¥648*	¥800*	5	100	58 x 15 x 9.6	20000	48	17
474-0211	MMEM58A-120	¥648*	¥800*	5	120	58 x 15 x 9.6	20000	56	17
474-0220	MMEM58A-150	¥648*	¥800*	5	150	58 x 15 x 9.6	20000	56	17
474-0238	MMEM58A-180	¥648*	¥800*	5	180	58 x 15 x 9.6	20000	56	17
474-0246	MMEM58A-240	¥648*	¥800*	5	240	58 x 15 x 9.6	20000	56	17
474-0254	MMEM58A-320	¥648*	¥800*	5	320	58 x 15 x 9.6	20000	56	17
474-0271	MMEM58A-400	¥648*	¥800*	5	400	58 x 15 x 9.6	20000	56	17

Zirconia (for stainless steel/difficult-to-cut material)

Order Unit: 5 Sheets

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Weight (g)
474-0327	MMEM58Z-40	¥648*	¥800*	5	40	58 x 15 x 9.6	20000	48	23
474-0335	MMEM58Z-60	¥648*	¥800*	5	60	58 x 15 x 9.6	20000	48	20
474-0343	MMEM58Z-80	¥648*	¥800*	5	80	58 x 15 x 9.6	20000	48	18
474-0301	MMEM58Z-100	¥648*	¥800*	5	100	58 x 15 x 9.6	20000	48	18
474-0319	MMEM58Z-120	¥648*	¥800*	5	120	58 x 15 x 9.6	20000	56	18

URL <http://www.miyuki-sangyo.jp/>

Please order items marked with * by no. of items in packet.

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes

5-951