

For Disc Grinders, see p. 5-209 to 226/For Oil Polishing Abrasives, see p. 5-1023 to 1025

TRUSCO

Stock
38,650
Items

"Felt Disc"

RoHS

Com
eco
Chemical Content
InspectionCom
Drawing
SDS

FD100

Estimated Unit Price per Sheet
¥2,688

- Features**
- Added cushioning function is a gentle luxury wool felt type.
 - Use oil-and-fat composition (green rouge, white bar, Tripoli) according to the application, and make a mirror surface finish.
- Use**
- Mirror surface finish polishing, glazing, wiping work.
- Specs**
- Max Working Peripheral Velocity: 41.9m/s (2512m/min)
 - Max Working Rotation Speed: 8000rpm
- Accessories**
- With 15mm hole adapter (1 piece per box)
- Origin**
- Japan



Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Hole Diameter (mm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
175-8284	FD100	¥13,438	¥16,590	100 x 10 x 16	5	20	230

Contact us:0120-509-849 <http://www.orange-book.com/>Grinding
WheelsDisk
PapersPapers for
Double
Action
SanderNylon
DiscsUrethane
DiscsFelt
DiscsDiamond
WheelsGrinding
Wheels

Dressers

Flap
WheelsNylon
Wheel
with ShaftShank
Mounted
Felt
Wheels
with Shaft

Bands

Shank
Mounted
StonesCarbide
BarsDiamond
BarsCBN
Bars

Files

Diamond
FilesGrinding
Stones

Abrasives

Sheet
Sanding
PapersAbrasive
BeltsCup
BrushesWheel
Brushes
with
ShankHand
Brushes

TRUSCO

Stock
38,650
Items

"Felt Disc α"

RoHS

Com
eco
Chemical Content
InspectionCom
Drawing
SDS

TFDA-100

Estimated Unit Price per Sheet
¥1,267

- Features**
- Depending on the applications, you can polish the wool felt with oil-and-fat composition.
 - A disc made from domestically produced fine felt.
- Use**
- Mirror surface finish polishing, wiping, finishing.
- Specs**
- Max Working Peripheral Velocity: 62.8m/s (3768m/min)
 - Max Working Rotation Speed: 12000rpm
- Accessories**
- With 15mm hole adapter (1 piece per box)
- Origin**
- Japan



Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Hole Diameter (mm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
261-2721	TFDA-100	¥6,334	¥7,820	100 x 10 x 16	5	20	295

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO

Stock
38,650
Items

"Felt Disc β"

RoHS

Com
Drawing

TFDB-100

Estimated Unit Price per Sheet
¥859

- Features**
- Mirror finish can be done by applying an oil polishing agent to felt. It can be used for wiping without applying an polishing agent.
- Use**
- Mirror surface finish polishing, wiping, finishing.
- Specs**
- Max Working Peripheral Velocity: 62.8m/s (3768m/min)
 - Max Working Rotation Speed: 12000rpm
- Accessories**
- With 15mm hole adapter (1 piece per box)
- Origin**
- Japan



Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Hole Diameter (mm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
402-6721	TFDB-100	¥4,293	¥5,300	100 x 10 x 16	5	20	325

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO

Stock
38,650
Items

"Beveled Disc Felt"

RoHS

Com
Drawing

TBD-10015F

Estimated Unit Price per Sheet
¥1,267

- Features**
- Since it is processed into an umbrella type special shape, the tip of the disc always hits the work and it can make a beautiful finish.
 - It has high flexibility and fits nicely on the work.
 - Since the mounting sole diameter is 15mm, it can be used with both electric and pneumatic grinders.
- Use**
- For glossing and creating mirror finishes on iron and stainless steel by applying an oil polishing agent (blue bar, etc.).
- Specs**
- Max Working Peripheral Velocity: 59.7m/s (3580m/min)
 - Max Working Rotation Speed: 12000rpm
- Origin**
- Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Hole Diameter (mm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
471-9701	TBD-10015F	¥6,334	¥7,820	95 x 10 x 15	5	20	290

Contact us:0120-509-849 <http://www.orange-book.com/>