

Prices displayed include 8% tax.

For Disc Grinders, see p. 5-209 to 226

TRUSCO

Stock 38,650 Items


"GP Disc Wheel" (direct screw-in type, vertical embedded type)



Chemical Content Inspection
 Drawing SDS

- Features**
- For general metal. Since there are gaps between the polishing cloths, clogging is prevented. As the base plate is smaller than the outer diameter of the polishing cloths, the bottom surface and side surface can be used for polishing at the same time.
 - There is heat dissipation, there is little distortion and burning of the object to be polished due to heat.
 - Can be installed with one touch (screw type).
- Use**
- Polishing prior to plating, metal surface polishing, and rust removal.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
- Materials**
- Alumina Abrasive Origin • Japan

Capable of polishing with two sides at the same time!



Example



GP100A-AL: 80

Estimated Unit Price per Sheet
¥583

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Screw Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
216-3161	GP100A-AL	40	¥2,916	¥3,600	40	100 x 15 x M10 (P1.5)	13600	80	5	20	450
216-3179	GP100A-AL	60	¥2,916	¥3,600	60	100 x 15 x M10 (P1.5)	13600	80	5	20	425
216-3187	GP100A-AL	80	¥2,916	¥3,600	80	100 x 15 x M10 (P1.5)	13600	80	5	20	400
216-3195	GP100A-AL	100	¥2,916	¥3,600	100	100 x 15 x M10 (P1.5)	13600	90	5	20	390
216-3209	GP100A-AL	120	¥2,916	¥3,600	120	100 x 15 x M10 (P1.5)	13600	90	5	20	380
216-3217	GP100A-AL	150	¥2,916	¥3,600	150	100 x 15 x M10 (P1.5)	13600	90	5	20	375
216-3225	GP100A-AL	180	¥2,916	¥3,600	180	100 x 15 x M10 (P1.5)	13600	90	5	20	375
216-3233	GP100A-AL	240	¥2,916	¥3,600	240	100 x 15 x M10 (P1.5)	13600	90	5	20	375
216-3241	GP100A-AL	320	¥2,916	¥3,600	320	100 x 15 x M10 (P1.5)	13600	90	5	20	365
216-3250	GP100A-AL	400	¥2,916	¥3,600	400	100 x 15 x M10 (P1.5)	13600	90	5	20	360

Contact us: 0120-509-849 <http://www.orange-book.com/>

YANASE

Stock 585 Items

"GP Disc"



- Features**
- As the polishing cloths are upright on the base plate, they are elastic and fit nicely around the item being processed.
 - As the diameter of the base plate is smaller than the outer shape of the polishing cloths, edges can be polished and it is also possible to polish two surfaces at the same time.
 - Does not generate heat and does not change the polished material.
- Use**
- Polishing prior to plating and polishing of metal surfaces.
 - Rust removal and burr removal.
 - Polishing of woodwork, plastics.
- Specs**
- Max Working Peripheral Velocity: 68m/s (4080m/min)
- Materials**
- Alumina Abrasive Origin • Japan

Example



GP100SA: 120

Order Unit: 10 Sheets

YANASE Co.Ltd

Order Code	Item No.	OP	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Weight (g)
322-4317	GP100SA	40	¥662*	¥980*	10	40	100 x 15 x 15	13000	80	75
322-4333	GP100SA	60	¥662*	¥980*	10	60	100 x 15 x 15	13000	80	75
322-4341	GP100SA	80	¥662*	¥980*	10	80	100 x 15 x 15	13000	80	75
322-4252	GP100SA	100	¥662*	¥980*	10	100	100 x 15 x 15	13000	80	75
322-4261	GP100SA	120	¥662*	¥980*	10	120	100 x 15 x 15	13000	90	63
322-4279	GP100SA	150	¥662*	¥980*	10	150	100 x 15 x 15	13000	90	63
322-4287	GP100SA	180	¥662*	¥980*	10	180	100 x 15 x 15	13000	90	63
322-4295	GP100SA	240	¥662*	¥980*	10	240	100 x 15 x 15	13000	90	63
322-4309	GP100SA	320	¥662*	¥980*	10	320	100 x 15 x 15	13000	90	63
322-4325	GP100SA	400	¥662*	¥980*	10	400	100 x 15 x 15	13000	90	61

Contact us: 0795-77-2151 <http://www.yanase-saving.com/>

ICHIGUCHI

Stock 1,066 Items

"BS Radial Wheel"



- Features**
- The paper makes soft contact and fits along uneven surfaces.
 - Made in Japan abrasive material is used.
- Use**
- Metal polishing, paint removal, and woodwork polishing.
- Specs**
- Max Working Peripheral Velocity: 69m/s (4100m/min)
- Materials**
- Alumina Abrasive Origin • China



63002

Order Unit: 1 Sheet

ICHIGUCHI CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	SPQ (sheet)	Weight (g)
410-3548	63001	¥711	¥810	40	100 x 15 x 15	13000	80	5	100
410-3556	63002	¥711	¥810	60	100 x 15 x 15	13000	80	5	84
410-3564	63003	¥711	¥810	80	100 x 15 x 15	13000	80	5	85
410-3572	63004	¥711	¥810	100	100 x 15 x 15	13000	80	5	80
410-3581	63005	¥711	¥810	120	100 x 15 x 15	13000	80	5	75

Contact us: 0774-94-9033 <http://www.ichiguchi.co.jp/>

Please order items marked with * by no. of items in packet.

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes