

Prices displayed include 8% tax.

For Disc Grinders, see p. 5-209 to 226

TRUSCO **Stock 38,650 Items**


## "Nylon Disc Mini"



**.Com Drawing**  
SDS



GPN50M (# 120)



Estimated Unit Price per Piece  
**¥596**

- Features**
- Nylon abrasive, which is made by sticking intertwined nylon fiber with abrasive, is used.
  - While the abrasive material of the paper polishing cloth directly strikes the polishing materials, the textile of nylon abrasive material acts as a cushion by the intertwined fiber and prevents the polishing materials from being excessively scraped.
  - Since it is large authigenesis, it does not get clogged.
- Use**
- Burn removal of stainless steel, aluminum, welded parts. For paint removal and creating mirror finishes.
- Specs**
- Max Working Peripheral Velocity: 15.7m/s (942m/min)
  - Outer diameter: 50mm**
- Origin**
- Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
172-9373	GPN50M	120	¥2,981	¥3,680	120	50 x 12 x 9.6	6000	38	5	1	93
172-9381	GPN50M	240	¥2,981	¥3,680	240	50 x 12 x 9.6	6000	40	5	1	73
172-9390	GPN50M	320	¥2,981	¥3,680	320	50 x 12 x 9.6	6000	45	5	1	83
172-9403	GPN50M	600	¥2,981	¥3,680	600	50 x 12 x 9.6	6000	45	5	1	96
172-9411	GPN50M	1000	¥2,981	¥3,680	1000	50 x 12 x 9.6	6000	45	5	1	68

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## "Nylon Disc Mini Hard"



**.Com Drawing**



TNDH58-120



Estimated Unit Price per Piece  
**¥648 to ¥680**

- Features**
- Since it uses a large volume of nylon, it has a long life.
  - Unlike whetstones, there is no worry of excessive grinding and this enables stable polishing.
- Use**
- Tough rust removal and black skin removal, etc.
  - Welding burn removal, paint removal, and finishing of stainless steel, etc.
- Specs**
- Maximum working peripheral velocity: 45.5m/s (2732m/min)
  - Outer Diameter: 58mm**
- Materials**
- Nylon non woven fabric
- Origin**
- Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
479-1738	TNDH58-120	¥3,402	¥4,200	Equivalent to 120	58 x 12 x 10	15000	5	20	145
479-1746	TNDH58-180	¥3,240	¥4,000	Equivalent to 180	58 x 12 x 10	15000	5	20	118
479-1754	TNDH58-320	¥3,240	¥4,000	Equivalent to 320	58 x 12 x 10	15000	5	20	94
479-1762	TNDH58-400	¥3,240	¥4,000	Equivalent to 400	58 x 12 x 10	15000	5	20	91

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## "GP Sander Nylon\*" (directly threaded type)



**.Com eco**  
Chemical Content Inspection

**.Com Drawing**  
SDS



GPSN8025 (outer diameter 80mm)

Outer Diameter 80mm  
Estimated Unit Price per Piece  
**¥1,215**

- Features**
- Dual purpose for stainless steel, general metal.
  - Polishing work is possible on 3 sides of the top, bottom and side.
  - Since intertwined nylon abrasive is used, it has cushioning and does not excessively scrape the polishing material, finishes only the surface.
  - Can do beautiful hairline processing by straight line work using the side.
  - Screw directly into the shaft of the disc grinder and install it.
- Use**
- Sealer sanding of R part, stainless steel, hairline processing of aluminum, woodwork, finishing before painting, mirror surface pre-processing of satin finish.
  - Working Tool: Disc Grinder/Straight-Type Grinder.
- Accessories**
- 6mm Shaft Adapters 1 piece per box (sold separately item no.: GPS-J6-1P)
- Origin**
- Japan



6mm Shaft Adapters (Item No.: GPS-J6-1P)

### Outer Diameter 80mm

- Specs**
- Max Working Peripheral Velocity: 25.1m/s (1507m/min)

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
116-9416	GPSN8025	120	¥6,075	¥7,500	120	80 x 25 x M10 (P1.5)	6000	38	5	20	365
116-9424	GPSN8025	240	¥6,075	¥7,500	240	80 x 25 x M10 (P1.5)	6000	40	5	20	250
116-9432	GPSN8025	320	¥6,075	¥7,500	320	80 x 25 x M10 (P1.5)	6000	40	5	20	270
116-9441	GPSN8025	600	¥6,075	¥7,500	600	80 x 25 x M10 (P1.5)	6000	50	5	20	250

### Outer Diameter 100mm

- Specs**
- Max Working Peripheral Velocity: 26.1m/s (1570m/min)

Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
116-9459	GPSN10025	120	¥7,695	¥9,500	120	100 x 25 x M10 (P1.5)	5000	51	5	20	520
116-9467	GPSN10025	240	¥7,695	¥9,500	240	100 x 25 x M10 (P1.5)	5000	52	5	20	425
116-9475	GPSN10025	320	¥7,695	¥9,500	320	100 x 25 x M10 (P1.5)	5000	52	5	20	425
116-9483	GPSN10025	600	¥7,695	¥9,500	600	100 x 25 x M10 (P1.5)	5000	59	5	20	425

Outer Diameter 100mm  
Estimated Unit Price per Piece  
**¥1,539**

Contact us:0120-509-849 <http://www.orange-book.com/>

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes