



Fitting series

SQSL , SQM series

CHELIC PNEUMATIC

◉ SQSL series Long elbow


Metric specification

Port size ØD	Thread size Rc (PT)	Model	A	B	C	E	ØG	L	Opposite dim H	Effective area mm ²	Weight (g)
Ø4	1/8"	SQSL 4 - 01	5.5	32.9	14.7	17.6	10.5	18.7	10	4.2	20
	1/4"	SQSL 4 - 02	9	33.8	14.7	17.6	10.5	21.7	14	4.2	36
Ø6	1/8"	SQSL 6 - 01	5.5	35.8	17.1	20.7	12.5	18.5	10	10	20
	1/4"	SQSL 6 - 02	8	37	17.1	20.7	12.5	21.3	14	10	32
Ø8	1/8"	SQSL 8 - 01	5.5	43.4	18.7	23	14.3	22.3	12	16	42.5
	1/4"	SQSL 8 - 02	8	44.6	18.7	23	14.3	24.9	14	16	43.5
	3/8"	SQSL 8 - 03	8	44.6	18.7	23	14.3	25.9	17	16	54
Ø10	1/4"	SQSL 10 - 02	8	53.4	20.9	26.6	17.8	27.4	17	30	62.5
	3/8"	SQSL 10 - 03	8	52.8	20.9	26.6	17.8	27.6	17	30	55.5
	1/2"	SQSL 10 - 04	11	55.7	20.9	26.6	17.8	30.9	21	30	60.5
Ø12	3/8"	SQSL 12 - 03	9	62.8	23.6	30.5	21.1	30.4	17	50	70
	1/2"	SQSL 12 - 04	10	62.6	23.6	30.5	21.1	33.9	21	50	96



Inch specification

Port size ØD	Thread size NPT	Model	A	B	C	E	ØG	L	Opposite dim H	Effective area mm ²	Weight (g)
5/32"	1/8"	SQSL 5/32 - 01	6	34.1	14.7	17.6	10.5	31.9	10	4.2	20
	1/4"	SQSL 5/32 - 02	9	35.6	14.7	17.6	10.5	34.9	14	4.2	36
1/4"	1/8"	SQSL 1/4 - 01	6	36.8	17	20.6	12.5	33.5	10	10	20
	1/4"	SQSL 1/4 - 02	9	37.8	17	20.6	12.5	36.5	14	10	32
5/16"	1/8"	SQSL 5/16 - 01	6	44.4	18.7	23	14.3	40.2	12	16	42.5
	1/4"	SQSL 5/16 - 02	9	45.9	18.7	23	14.3	43.2	14	16	43.5
	3/8"	SQSL 5/16 - 03	9	45.9	18.7	23	14.3	43.2	17	16	54
3/8"	1/4"	SQSL 3/8 - 02	9	54.7	21.3	27	17.8	50.3	17	30	66
	3/8"	SQSL 3/8 - 03	9	54.1	20.3	26.4	17.8	49.7	17	30	58
1/2"	3/8"	SQSL 1/2 - 03	9	62.9	24.2	31.1	21.1	56.8	17	50	72
	1/2"	SQSL 1/2 - 04	11	64	19.8	26.7	21.1	58.9	21	50	96



◉ SQM series Branch double Y

Metric specification

Port size ØD	Thread size Rc (PT)	Model	A	B	C	Ød	ØG	J	L	Opposite dim H	Effective area mm ²	Weight (g)
Ø6	1/8"	SQM 6 - 01	6	45.4	17	3.2	12.4	12.4	48.4	10	10	25
	1/4"	SQM 6 - 02	9	47.5	17	3.2	12.4	12.4	52	14	10	29



Inch specification

Port size ØD	Thread size NPT	Model	A	B	C	Ød	ØG	J	L	Opposite dim H	Effective area mm ²	Weight (g)
1/4"	1/8"	SQM 1/4 - 01	6	45.5	17	3.2	12.4	12.4	48.5	10	10	25
	1/4"	SQM 1/4 - 02	9	47.6	17	3.2	12.4	12.4	52.1	14	10	29

