




Fitting series

SQT series

CHELIC PNEUMATIC

◉ SQT series Branch tee

Metric specification



Port size ØD	Thread size Rc (PT)	Model	A	B	C	E	ØG	L	Opposite dim H	Effective area mm ²	Weight (g)
Ø4	M5	SQT 4 - M5	2.2	19.4	14.5	17.4	10.5	15.3	10	3.5	8
	1/8"	SQT 4 - 01	5.5	21.2	14.5	17.4	10.5	18.7	10	4.2	12
	1/4"	SQT 4 - 02	8	22.9	14.5	17.4	10.5	21.7	14	4.2	18
Ø6	M5	SQT 6 - M5	2.5	23.8	17.1	20.7	12.4	18.8	10	3.5	11.5
	1/8"	SQT 6 - 01	5.5	26.1	17.1	20.7	12.4	22.6	10	10	13.5
	1/4"	SQT 6 - 02	8	28.1	17.1	20.7	12.4	25.9	14	10	20.5
Ø8	3/8"	SQT 6 - 03	8	29.6	17.1	20.7	12.4	27.4	17	10	25.5
	1/8"	SQT 8 - 01	5.5	26.7	18.6	22.9	14.3	22.3	12	16	16.5
	1/4"	SQT 8 - 02	8	28	18.6	22.9	14.3	24.9	14	16	22.5
Ø10	3/8"	SQT 8 - 03	8	29	18.6	22.9	14.3	25.9	17	16	27
	1/8"	SQT 10 - 01	5.5	30.8	20.9	26.6	17.8	24.6	17	16	32
	1/4"	SQT 10 - 02	8	32.3	20.9	26.6	17.8	27.4	17	30	34
	3/8"	SQT 10 - 03	8	32.5	20.9	26.6	17.8	27.6	17	30	35
Ø12	1/2"	SQT 10 - 04	10	34.8	20.9	26.6	17.8	30.9	21	30	50
	1/4"	SQT 12 - 02	8	37	23.7	30.6	21.2	30.4	17	50	48
	3/8"	SQT 12 - 03	8	37	23.7	30.6	21.2	30.4	17	50	51
	1/2"	SQT 12 - 04	10	39.5	23.7	30.6	21.2	33.9	21	50	63

SQ
Fitting

MSQ
Mini type
Fitting

SP
Plug
Nipple

SQ J
Nipple
Fitting

SQR
Check
Fitting

SQ G
Pressure
Gauge
Fitting

**Brass
Fitting**

Inch specification

Port size ØD	Thread size NPT	Model	A	B	C	E	ØG	L	Opposite dim H	Effective area mm ²	Weight (g)
5/32"	NR 10/32"	SQT 5/32 - 10/32	2.4	20.4	14.5	17.4	10.5	16.4	10	3.5	8
	1/8"	SQT 5/32 - 01	6	22.4	14.5	17.4	10.5	20.2	10	4.2	12
	1/4"	SQT 5/32 - 02	9	24.1	14.5	17.4	10.5	23.4	14	4.2	18
1/4"	NR 10/32"	SQT 1/4 - 10/32	2.5	23.8	17	20.6	12.4	18.8	10	3.5	11.5
	1/8"	SQT 1/4 - 01	6	25.8	17	20.6	12.4	22.6	10	10	13.5
	1/4"	SQT 1/4 - 02	9	27.6	17	20.6	12.4	25.9	14	10	20.5
	3/8"	SQT 1/4 - 03	9	29.1	17	20.6	12.4	27.4	17	10	25.5
5/16"	1/8"	SQT 5/16 - 01	6	27.5	18.6	22.9	14.3	23.4	12	16	16.5
	1/4"	SQT 5/16 - 02	9	29.3	18.6	22.9	14.3	26.7	14	16	22.5
	3/8"	SQT 5/16 - 03	9	30	18.6	22.9	14.3	27.4	17	16	27
3/8"	1/8"	SQT 3/8 - 01	6	31.7	21.3	27	17.8	25.8	17	16	32
	1/4"	SQT 3/8 - 02	9	33.4	21.3	27	17.8	29	17	30	34
	3/8"	SQT 3/8 - 03	9	34.1	21.3	27	17.8	29.7	17	30	35
	1/2"	SQT 3/8 - 04	11	36.1	20.3	26.4	17.8	32.7	21	30	50
1/2"	1/4"	SQT 1/2 - 02	9	38.3	24.3	31.2	21.2	32.2	17	50	48
	3/8"	SQT 1/2 - 03	9	38.3	24.3	31.2	21.2	32.2	17	50	51
	1/2"	SQT 1/2 - 04	11	30.9	22.8	29.7	22.3	35.2	21	50	63

SC
Speed
Controller

QS
Speed
Controller

QH
Hand
Valve

QV
Union
Straight

QST
Panel type
Speed
Controller

**PU
Tube**