

**Disk Dia. 50mm** Handy & powerful grinder pursuing safety and usability.

**No. GT-DG50**



**Disk Dia. 100mm** Handy & powerful grinder pursuing safety and usability.

**No. GT-DG100**



**OP**  
Bar grip (Auxiliary handle)

Model No.	Grindstone Size Outer Dia.×Thickness×Hole Dia. (mm)	Max Operating Circumferential Speed(m/s)	No Load Speed (rpm)	Air Consumption (m <sup>3</sup> /min)	Hose Coupling	Overall Length (mm)	Height (mm)	Weight (g)	Accessories		EDP No.
									Plug	L-wrench	
<b>GT-DG50</b>	50×4×9.5	39.2	15,000	0.57	Rc 1/4	164	70	800	BPB-2	H6	310639
<b>GT-DG100</b>	100×6×15	70.6	13,500	0.7	Rc 1/4	205	92	1,390	BPB-2	H6	310630

·Air pressure: 0.6MPa ·Air hose diameter: 6.35mm

## One point

### Application

### Wheel

### Tools

- For removing burr from thin metal sheet press, cutter mark, burr from aluminum casting, wood work, etc.



**No. GT-DS50A**



- For removing slag and spatter after welding, rust on steel members, burr on foundry pieces, shells on ship bottom, etc.



**No. GT-DS50B**

