



SLP series - Slinger (Polyethylene resin)

Specification and External dimension

CHELIC PNEUMATIC



CJ-M
Float joint

M□V
Manually operated valve

SA□
Shock absorber

SHR
Hydraulic regulator


SL□
Slinger

P□S
Rod end

Specification

Item	Model	SLP-01	SLP-02	SLP-02L	SLP-03	SLP-04	SLP-06	SLP-10
Fluid		Air						
Range of service pressure	kgf/cm ² (kpa)	0 ~ 9 (900)						
Ensure withstanding pressure	kgf/cm ² (kpa)	11 (1100)						
Range of service temperature	°C	5~60						
Material	Body	Polyethylene resin						
	Filter element	Foam resin (5µm)						
Connection port	Rc (PT)	1/8"	1/4"		3/8"	1/2"	3/4"	1 "

External dimension



Model	Code	Connection port R Rc (PT)	A	B	C	Cross flat distance H
SLP - 01		1/8"	7	34	16	14
SLP - 02		1/4"	10	37	16	14
SLP - 02L		1/4"	10	62	20	16.8
SLP - 03		3/8"	12	67	26	24
SLP - 04		1/2"	15	70	28	24
SLP - 06		3/4"	16	99.3	40	31.5
SLP - 10		1 "	19	119	47.8	35.5