



Fitting series


SQU series

CHELIC PNEUMATIC

◉ SQU series Branch Y

Metric specification

Port size ØD	Thread size Rc (PT)	Model	A	B	C	J	ØG	L	Opposite dim H	Effective area mm ²	Weight (g)
Ø4	M5	SQU 4 - M5	2.2	29.9	14.5	10.5	10.5	31	10	3.5	8.5
	1/8"	SQU 4 - 01	5.5	31.6	14.5	10.5	10.5	34.4	10	4.2	12
	1/4"	SQU 4 - 02	8	33.4	14.5	10.5	10.5	37.4	14	4.2	8.5
Ø6	M5	SQU 6 - M5	2.5	35.3	17.1	12.3	12.3	36.6	10	3.5	11.5
	1/8"	SQU 6 - 01	6	37.6	17.1	12.3	12.3	40.4	10	10	13.5
	1/4"	SQU 6 - 02	9	39.1	17.1	12.3	12.3	43.6	14	10	20.5
Ø8	3/8"	SQU 6 - 03	9	40.7	17.1	12.3	12.3	45.2	17	10	25.5
	1/8"	SQU 8 - 01	5.5	38.7	18.6	14.3	14.3	41.4	12	16	17
	1/4"	SQU 8 - 02	8	40	18.6	14.3	14.3	44	14	16	23
Ø10	3/8"	SQU 8 - 03	8	41	18.6	14.3	14.3	45	17	16	28
	1/8"	SQU 10 - 01	5.5	43.6	20.9	17.8	17.8	46.4	17	16	32
	1/4"	SQU 10 - 02	8	45.2	20.9	17.8	17.8	49.2	17	30	34
Ø12	3/8"	SQU 10 - 03	8	45.4	20.9	17.8	17.8	49.4	17	30	35
	1/2"	SQU 10 - 04	10	47.7	20.9	17.8	17.8	52.7	21	30	52
	1/4"	SQU 12 - 02	8	49.4	23.6	21.2	21.2	53.4	17	50	44
Ø12	3/8"	SQU 12 - 03	8	50.4	23.6	21.2	21.2	54.4	17	50	47
	1/2"	SQU 12 - 04	10	51.9	23.6	21.2	21.2	56.9	21	50	60



SQ
Fitting

MSQ
Mini type
Fitting

SP
Plug
Nipple

SQ J
Nipple
Fitting

SQR
Check
Fitting

SQ G
Pressure
Gauge
Fitting

**Brass
Fitting**

Inch specification

Port size ØD	Thread size NPT	Model	A	B	C	J	ØG	L	Opposite dim H	Effective area mm ²	Weight (g)
5/32"	NR 10/32"	SQU 5/32 - 10/32	2.4	30.9	14.5	10.5	10.5	32.1	10	3.5	8.5
	1/8"	SQU 5/32 - 01	6	32.9	14.5	10.5	10.5	35.9	10	4.2	12
	1/4"	SQU 5/32 - 02	9	34.6	14.5	10.5	10.5	39.1	14	4.2	8.5
1/4"	NR 10/32"	SQU 1/4 - 10/32	2.5	35.3	17	12.3	12.3	36.5	10	3.5	11.5
	1/8"	SQU 1/4 - 01	6	37.3	17	12.3	12.3	40.3	10	10	13.5
	1/4"	SQU 1/4 - 02	9	39.1	17	12.3	12.3	43.6	14	10	20.5
5/16"	3/8"	SQU 1/4 - 03	9	40.6	17	12.3	12.3	45.1	17	10	25.5
	1/8"	SQU 5/16 - 01	6	39.5	18.6	14.3	14.3	42.5	12	16	17
	1/4"	SQU 5/16 - 02	9	41.3	18.6	14.3	14.3	45.8	14	16	23
3/8"	3/8"	SQU 5/16 - 03	9	42	18.6	14.3	14.3	46.5	17	16	28
	1/8"	SQU 3/8 - 01	6	44.9	21.3	17.8	17.8	47.9	17	16	32
	1/4"	SQU 3/8 - 02	9	46.7	21.3	17.8	17.8	51.2	17	30	34
1/2"	3/8"	SQU 3/8 - 03	9	47.4	21.3	17.8	17.8	51.9	17	30	35
	1/2"	SQU 3/8 - 04	11	47.7	21.3	17.8	17.8	52.7	21	30	52
	1/4"	SQU 1/2 - 02	9	51.3	24.2	21.2	21.2	55.8	17	50	44
1/2"	3/8"	SQU 1/2 - 03	9	51.3	24.2	21.2	21.2	55.8	17	50	47
	1/2"	SQU 1/2 - 04	11	51.9	24.2	21.2	21.2	56.9	21	50	60

SC
Speed
Controller

QS
Speed
Controller

QH
Hand
Valve

QV
Union
Straight

QST
Panel type
Speed
Controller

**PU
Tube**