

## Fuse terminals

In hazardous area applications, the installation instructions and the rated data specifications for accessories given in the technical appendix must be followed.

Width/Length/height with TS35x7.5	mm
max. current / max. cond. cross-section	A/mm <sup>2</sup>
Max. clamping range	mm <sup>2</sup>

### Technical data

Rated data	
Rated voltage	V
Rated current	A
Rated cross-section	mm <sup>2</sup>
Rated impulse voltage / Pollution severity	V/-
Gauge to IEC 60947-1 / UL94 Flammability class	Approvals

#### Clamped conductors (H05V/H07V)

solid / stranded	mm <sup>2</sup>
flexible / Stranded wire with end ferrules	mm <sup>2</sup>
Tightening torque range (clamping screw)	
Stripping length / Blade size	mm/-

#### 2 conductors with same cross-section (H05V/H07V)

solid / stranded	mm <sup>2</sup>
flexible / Stranded wire with end ferrules	mm <sup>2</sup>

#### Note

### Ordering data

Version	
400 V AC/DC, without LED	
10-36 V AC/DC, with LED	
30-70 V AC/DC, with LED	
60-150 V AC/DC, with LED	
140-250 V AC/DC, with LED	

#### Note

### Accessories

#### Screwable cross-connection



- 2-pole
- 3-pole
- 4-pole
- 10-pole

#### End plate / partition

- Dark beige Wemid
- Dark beige Wemid

#### Screwdriver

- with „swifty set“ cutting device
- Standard

#### G-fuse cartridge, 5 x 20mm (IEC 60127-2)

- 0,25 A fast
- 0,50 A fast
- 1,00 A fast
- 2,00 A fast

#### G25 with indicator / imperial (inch) fuse

- 0,50 A medium slow / 2 A
- 1,00 A medium slow / 3 A
- 2,00 A fast / 5 A
- 4,00 A fast / 10 A


#### Marking systems

- (see assortment in catalogue 7)
- Marking tags

For detailed information on other accessories and applications, refer to the „Accessories“ section

## WSI 4/2

4 mm<sup>2</sup>



9.1 x 81.6 x 54

15 / 4

0.5...4



IEC 60947-7-3

IEC	UL	CSA
500	300	300
15	15	15
4	AWG 22...10	AWG 22...10
6 /		
A3 / V-0		



#### Rated connection

0.5...4 / 0.5...4
0.5...4 / 0.5...4
0.5...0.8 Nm (M 3)
10 / 0.6 x 3.5 mm

0.5...1.5

0.5...1.5 / 0.5...1.5

width x length x height with TS 32 = 9.1 x 81.6 x 58.5 mm

Type	Qty	Order No.
WSI 4/2	25	1880430000
WSI 4/2/LD 10-36V AC/DC	25	1880410000
WSI 4/2/LD 30-70V AC/DC	25	1880440000
WSI 4/2/LD 60-150V AC/DC	25	1880420000
WSI 4/2/LD 140-250V AC/DC	25	1880390000

#### Type

Type	Qty	Order No.

#### Width

WAP WSI4/2	50	1880450000
------------	----	------------

#### SWIFTY SET

SD 0.6x3.5x100	1	9008330000
----------------	---	------------

#### GZ 2.0A

GZ 2.0A	10	0294500000
---------	----	------------

#### GZ 3.0A

GZ 3.0A	10	0295700000
---------	----	------------

#### GZ 5.0A

GZ 5.0A	10	0294600000
---------	----	------------

#### GZ 10.0A

GZ 10.0A	10	0293900000
----------	----	------------

DEK 5/5 / WS 12/6

Dummy cartridge fuse order No. 1582770000

## WSI 4

4 mm<sup>2</sup>



8 x 50.7 x 39.4

15 / 4

0.5...4



IEC 60947-7-3

IEC	UL	CSA
500	300	300
12	15	15
4	AWG 22...12	AWG 22...12
6 / 3		
A3 / V-0		



#### Rated connection

0.5...4 / 0.5...4
0.5...4 / 0.5...4
0.5...0.8 Nm (M 3)
8 / 0.6 x 3.5 mm

0.5...1.5

0.5...1.5 / 0.5...1.5

Type	Qty	Order No.
WSI 4	50	1886580000
WSI 4/LD 10-36V AC/DC	50	1886590000
WSI 4/LD 30-70V AC/DC	50	1886560000
WSI 4/LD 60-150V AC/DC	50	1886570000
WSI 4/LD 140-250V AC/DC	50	1886550000

#### Type

Type	Qty	Order No.

#### SWIFTY SET

SD 0.6x3.5x100	1	9008330000
----------------	---	------------

#### G 20/0.25A/F

G 20/0.25A/F	10	0430500000
--------------	----	------------

#### G 20/0.50A/F

G 20/0.50A/F	10	0430600000
--------------	----	------------

#### G 20/1.00A/F

G 20/1.00A/F	10	0430700000
--------------	----	------------

#### G 20/2.00A/F

G 20/2.00A/F	10	0430900000
--------------	----	------------

DEK 5/5 / WS 12/6