

















ステンレス鋼製ねじ込み管継手

エルボ		L		45°エルボ		45°L	
				呼び (B)	L	呼び (B)	L1
1/8	19	1 1/4	45	1/8	18	1 1/4	33
1/4	21	1 1/2	50	1/4	18	1 1/2	37
3/8	23	2	57	3/8	20	2	43
1/2	27	2 1/2	70	1/2	23.5	2 1/2	50
3/4	33	3	78	3/4	25	3	55
1	38	4	98	1	29	4	64

ストリートエルボ			SL			径違いエルボ			RL					
				呼び (B)	L	L1	呼び (B)	L1	L2	呼び (B)	L1	L2		
1/8	25	19	1 1/4	60	45	1/4x1/8	23	23.5	1x1/2	32	34	2x1/4	48	54
1/4	28	21	1 1/2	65	50	3/8x1/4	20	22	1x3/4	37.5	33.5	1/2x1/4	24	24
3/8	32	25	2	74	58	1/2x1/4	24	24	1 1/4x3/4	38	40	1/2x3/8	26	25.5
1/2	42.5	28	2 1/2	100	69	1 1/4x1	39.5	40.5	1 1/2x1	41.5	45	3/4x3/8	28	28
3/4	50.5	33	3	114	76.5	1 1/2x1 1/4	45	48	3/4x1/2	34	28	2x1/2	52	55
1	52	39	4											

プラグ			P			キャップ			CA		
				呼び (B)	L	SW	呼び (B)	L	呼び (B)	L	
1/8	16.5	7	1 1/4	35	24	1/8	15	1 1/4	32.5		
1/4	20	9	1 1/2	37	25	1/4	17	1 1/2	34.5		
3/8	22	11	2	39	32	3/8	17	2	38		
1/2	25	13.5	2 1/2	48	42	1/2	19	2 1/2	42		
3/4	27.5	16	3	52	46	3/4	24.5	3	47		
1	32	20	4	62	58	1	29.5	4	54		

ホースニップル						HONI						ニップル			HXNI		
				呼び (B)	L	L1	A	C	SW	呼び (B)	L	SW	呼び (B)	L	SW		
1/8	45	25	6.5	3.3	13	1 1/4	81	46	33	25.8	46	1/8	29	12.5	1 1/4	56	46
1/4	47	24	9	5.6	17	1 1/2	95	59.5	39.5	32.4	52.5	1/4	32.5	17	1 1/2	59.5	52
3/8	55	34.5	11	7.2	20	2	106	64.5	52	43.2	63	3/8	36.5	20	2	65	62.5
1/2	64	40	14	9.4	24							1/2	43	26	2 1/2	81	79
3/4	68	40.5	20.5	14.6	31.5							3/4	46	32	3	90	92.5
1	71	40	27	18.2	39							1	52	38	4	107	118

※エルボ・ストリートエルボ・チースに関して、1/8~2はバンド無(平形)もございます。

単位: mm