

## Power Scaler

- The barycenter is at the front side, alleviating the strain on your wrist. Downward-facing work on a welding bench is easy and effortless.
- With a new shape similar to the straight type, it can be handled smoothly even in places set deep at a place where the pistol types cannot reach.
- Needles do not spread as much, enabling to aim at the welding spatters and to perform a precise work.
- Easy to replace needles without any tools.
- The hose rotates 360°, making it easier to handle. Equipped with a filter to prevent dust coming in from the air inlet.
- Convenient for removing spatters or slugs, peeling off coating and removing rust.



Needle  $\phi$ 2mm

### No. GT-HPS160

- Needle  $\phi$ 2mm×180mm ..... 29pcs.
- Accessories ·Hose set ..... 1set
- Hydraulic oil for hammer unit 1pc. (VG-10·White)
- Replacement needles ..... 29pcs. ( $\phi$ 2mm×180mm)



Needle  $\phi$ 3mm

### No. GT-HPS200

- Needle  $\phi$ 3mm×180mm ..... 12pcs.
- Accessories ·Hose set ..... 1set
- Hydraulic oil for hammer unit 1pc. (VG-10·White)
- Replacement needles ..... 12pcs. ( $\phi$ 3mm×180mm)

Model No.	Piston diameter (mm)	Needle stroke (mm)	Number of impacts (min <sup>-1</sup> )	Air Consumption (m <sup>3</sup> /min)	Inlet bushing	Appropriate Air Pressure (MPa)	Air hose inner diameter (mm)	Overall length (mm)	Weight (kg)	EDP No.
GT-HPS160	16	18	4000	0.22	Rc 1/4	0.6	6.35	380	1.47	310650
GT-HPS200	20	20	3700	0.26	Rc 1/4	0.6	6.35	400	1.9	310651


\*Overall length and weight : Accessories included

## Needles for Power Scalers

### No. HPSN-215



### No. HPSN-318



### No. HPSN-218



### For GT-HPS160 (100pieces)

Model No.	Contents	EDP No.
HPSN-215	$\phi$ 2mm×150mm 100pcs.	350151
HPSN-218	$\phi$ 2mm×180mm 100pcs.	350150

### For GT-HPS200 (50pieces)

Model No.	Contents	EDP No.
HPSN-318	$\phi$ 3mm x180mm 50pcs.	350152