


Unit No. and Dimensions of Withdrawal Sleeve-series: AH23

取りはずしスリーブ
Withdrawal Sleeve

Series AH 23



呼び番号 Nominal No.	スリーブ主要寸法 Boundary Dimension (mm)						参考 Reference		スリーブ重量 Weight (kg)
	d ₁	ネジ呼び(D ₁)×ピッチ Screw (D ₁)×Pitch	L	L ₁	b	a	ナット呼び番号 Unit No. of Nut	軸内径番号 Brg. Inner dia No.	
AH 2308	35	M 45×1.5	40	43	7	10	AN 09	08	0.128
AH 2309	40	50×1.5	44	47	7	11	10	09	0.164
AHX 2310	45	55×2	50	53	9	15	11	10	0.209
AHX 2311	50	M 60×2	54	57	10	16	AN 12	11	0.253
AHX 2312	55	65×2	58	61	11	17.5	13	12	0.297
AH 2313	60	75×2	61	64	12	15	15	13	0.395
AHX 2314	65	M 80×2	64	68	12	15	AN 16	14	0.466
AHX 2315	70	85×2	68	72	12	15	17	15	0.534
AHX 2316	75	90×2	71	75	12	15	18	16	0.597
AHX 2317	80	M 95×2	74	78	13	16	AN 19	17	0.670
AHX 2318	85	100×2	79	83	14	17	20	18	0.779
AHX 2319	90	105×2	85	89	16	19	21	19	0.886
AHX 2320	95	M 110×2	90	94	16	19	AN 22	20	0.998
AHX 2322	105	125×2	98	102	16	19	25	22	1.35
AHX 2324	115	135×2	105	109	17	20	27	24	1.60
AHX 2326	125	M 145×2	115	119	19	22	AN 29	26	2.00
AHX 2328	135	155×3	125	130	20	23	31	28	2.33
AHX 2330	145	165×3	135	140	24	27	33	30	2.82
AH 2332	150	M 180×3	140	146	24	27	AN 36	32	4.70
AH 2334	160	190×3	146	152	24	27	38	34	5.30
AH 2336	170	200×3	154	160	26	29	40	36	5.90
AH 2338	180	TM 210×4	160	167	26	32	HN 42	38	6.50
AH 2340	190	220×4	170	177	30	36	44	40	7.50
AH 2344	200	240×4	181	189	30	36	48	44	13.4
AH 2348	220	TM 260×4	189	197	30	36	HN 52	48	15.5
AH 2352	240	290×4	205	213	30	36	58	52	20.0
AH 2356	260	310×5	212	220	30	36	62	56	21.5

- [注] 1. Mはメートル系ネジ, TMは30°台形ネジ, 数字はネジ外径およびピッチを示します。
 2. 背割りは必要に応じて1個以上設けることができます。
 3. 記号A Hの後に記号Xをつけた取りはずしスリーブは, 従来用いられていたものと呼び内径(d₁)またはネジ寸法が異なるものです。(15頁の従来寸法の取りはずしスリーブ表を参考にして下さい)

- N.B.- 1. The mark "M" shows metric screw Thread, "TM-" shows 30° Trapezoidal Screw Thread and "numeral" shows Thread outer diameter and pitch.
 2. It is able to make Grove in one point or more as occasion demands.
 3. Withdrawal Sleeves with mark "AHL" are different from the usual dimensions in inner diameter and thread. (Ref. P 15 "Classification of Withdrawal Sleeve in the usual dimensions")