



MR TYPE



MR-75N



● Description of product number

MR - 75 N

Bracket type
Wheel diameter
Wheel type

Bracket = Trivalent unichrome coating

Product number	Wheels								
		Wheel diameter D(mm)	Wheel width W(mm)	Mounting height H(mm)	Mounting base A × B(mm)	Mounting dimensions X × Y(mm)	Hole diameter P(mm)	Allowance load daN(kgf)	Wheel weight (g)
MR-65	N Nylon wheel	65	28	82	113 × 59	89 × 28	8.5	90(91.8)	300
MR-75	N Nylon wheel	75	35	93	127 × 65	100 × 30	8.5	100(102.0)	405

Wheel in use

Refer to P160 for detailed specifications.



N Nylon wheel

- J
- PM
- J2
- RJ2
- SJ
- S
- E
- G
- L
- SA
- H
- CAL -H
- M
- PL
- Silence
- SUS -J2
- SUS -SJ
- SUS -S
- SUS -E
- SUS -H
- P
- SKY
- Equipped with adjuster foot
- Special
- Easy lock
- Wheels