

SUS-SK TYPE



There are some non-conforming products.



Fixed wheel




Plate type





Stainless steel




SUS-SK-100GU



*SUS-SK-100



*SUS-SK-125



● Description of product number

SUS - SK - 100 GU

Bracket type

Wheel diameter

Wheel type

Bracket = Stainless steel

Product number	Wheels								
		Wheel diameter D(mm)	Wheel width W(mm)	Mounting height H(mm)	Mounting base A × B(mm)	Mounting dimensions X × Y (X' × Y') (mm)	Hole diameter P(mm)	Allowance load daN(kgf)	Wheel weight (g)
SUS-SK-100	NR Rubber wheel with nylon wheel assembly (including B)	100	32	132	110 × 75	90 × 50 (80 × 45)	11	100(102.0)	630
	N Nylon wheel							100(102.0)	540
	NB Nylon wheel (including B)							100(102.0)	620
	GU Urethane wheel with nylon wheel assembly (including B)							100(102.0)	660
SUS-SK-125	GU Urethane wheel with nylon wheel assembly (including B)	125	32	168	135 × 100	112 × 53 (100 × 56)	11	120(122.4)	980

※ Mounting dimensions of SUS-SK-125 is X + Y'(X' + Y)

Wheel in use

Refer to P162 for detailed specifications.



NR

Rubber wheel with nylon wheel assembly (including B)



N

Nylon wheel



NB

Nylon wheel (including B)



GU

Urethane wheel with nylon wheel assembly (including B)