

# AO-2

## ■Features

1. Body larger than nominal size slows the velocity of water, and the baffle effectively separates air.
2. Prevents noise of water hammer caused by air.
3. Prevents corrosion of piping system caused by air.



## ■Specifications

Application	Cold and hot water
Max. pressure	1.0 MPa
Max. temperature	120°C
Material	Bronze
Connection	JIS Rc screwed

## ■Dimensions (mm) and Weights (kg)

Nominal size	d	L	H	H <sub>1</sub>	d <sub>2</sub>	Weight
20A	Rc 3/4	120	84	27.5	Rc 1/2	1.1
25A	Rc 1	140	84	27.5	Rc 1/2	1.2
32A	Rc 1-1/4	155	113.5	33.5	Rc 1/2	2.0
40A	Rc 1-1/2	205	136.5	43.5	Rc 1/2	3.6
50A	Rc 2	205	136.5	43.5	Rc 1/2	3.8

