


Shaft Supports Side Mount (Machined)

Standard / Slit


■ **Features:** Enables to mount on the plate side.

■ **Standard**




RoHS10

Type	M Material	S Surface Treatment	A Accessory
SHQB	S45C	Black Oxide	Hex Socket Set Screw 1 pc.
SHQM	Equivalent	Electroless Nickel Plating	Hex Socket Set Screw 1 pc. (SUS)



Part Number Type	D	H Selection				L	H1	H2	T	L1	d	Set Screw M	Unit Price	
		25	30	40	50								SHQB	SHQM
SHQB SHQM	8	25	30			22	H+9	5	12	10	4.5	4		
	10	25	30				H+10							
	12	25	30				H+11							
	13	25	30			25	H+12			14	4.5	4		
	15	25	30	40			H+15							
	16	25	30	40										
	18	25	30	40	50	28				16	6.6	6		
	20	25	30	40	50		H+18							
	25	30	40	50			H+20							
	30	30	40	50	60	32	H+23			18	9	6		
	35	40	50	60			H+25							
	40	40	50	60			H+30							


■ **Slit Type**



RoHS10

Type	M Material	S Surface Treatment	A Accessory
SHYB	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHYM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 1 pc. (SUS)
SHYS	SUS304	-	
SHYA	Aluminum Alloy	Clear Anodize	

⚠ Slit is machined after the mounting hole D is bored to H7 tolerance. The tolerance may become H8 or so depending on the machining condition.




Part Number Type	D	H Selection				L	H1	H2	T	L1	E	d	Tightening Screw M	d2	d1	l	C	Unit Price			
		20	25	30	40													SHYB	SHYM	SHYS	SHYA
SHYB SHYM SHYS SHYA	8	20	25	30		22	H+16	5	12	10	11	4.5	M4 Depth 8	4.5	8	4.5	2				
	10	20	25	30			H+18														
	12	20	25	30			H+20														
	13	20	25	30		25				14	13	4.5	M6 Depth 12	6.6	11	6.5					
	15	25	30	40			H+26														
	16	25	30	40			H+28														
	18	25	30	40	50	28				16	15	6.6	M	9	14	9	3				
	20	25	30	40	50		H+33														
	25	30	40	50			H+36														
	30	30	40	50	60	32	H+38			18	18	9	M	9	14	9	3				
	35	40	50	60			H+38														
	40	40	50	60																	

⚠ Values in () are the T dimensions of SHYA (Aluminum).

Ordering Example: Part Number - H
 SHQM16 - 25
 SHYS12 - 30

Alterations: Part Number - HC
 SHQM16 - HC35.6
 SHYS40 - HC35.6
 SHYS40 - HC50.5

Alteration	Code	Spec.
	HC	Changes shaft mounting height. Change H to specify height. ⚠ Specify HC in 0.1mm increments. ⚠ Specifiable Range Hmin. < HC < Hmax. [Ordering Code] HC35.6