


Conveyor Aluminum Extrusion

Dedicated web site <http://fa.misumi.jp/cvs/>
 Conveyor selecting, component purchases, and easy search for maintenance parts are available.



Part Number Type	L No.	Applicable Conveyors	Max. Belt Width	Mass kg/m	Sectional Area mm ²	Moment of Inertia of Area							
						I_x	I_y						
HFSDCV	2990	SVKA	50	1.99	733	6.35x10 ⁴	80.05x10 ⁴						
		SVKB	100	2.94	1,081	7.66x10 ⁴	252.97x10 ⁴						
		SVKN	150	3.35	1,231	8.40x10 ⁴	534.16x10 ⁴						
		SVKR	200	4.28	1,573	9.26x10 ⁴	1028.47x10 ⁴						
		SVKRL	250	4.82	1,773	9.72x10 ⁴	1662.85x10 ⁴						
	2825	100~3000	CVSFA	-	1.19	440	3.425x10 ⁴	1.875x10 ⁴					
			CVSFC										
			CVSJA										
			CVGA										
			CVGB										
			CVSFB										
			CVSFD										
			CVSSA										
			CVGC										
			CVGD										
	4830	100~3000	CVGN	-	2.51	928	5.90x10 ⁴	16.57x10 ⁴					
CVGP													
CVGR													
CVGW													
CVGTB													
CVGTP													
CVSTC-20													
CVSTR-20													
6828			90~3000	CVSMA					-	2.37	879	6.11x10 ⁴	29.45x10 ⁴
2820			100~3000	CVSTC-10					10	0.78	287	2.21x10 ⁴	0.92x10 ⁴
6630		CVSPA	20	2.3	851	23.74x10 ⁴	7.36x10 ⁴						



Ordering Example

Part Number
 Type - No. - L
HFSDCV - 2990 - 500