



Chain Guides with Steel Frame / Chain Guides

L Dimension Selectable / Configurable

■ **Features:** By passing a chain through this type of guide, conveyance is provided with little dust/noise.



■ L Dimension Selectable w/o Hole Machining

Part Number	No.	L Length Selection (mm)	A	B	C	D	E	F	G	H	t	Mass (kg/m)	Unit Price						
													GDTC, GDCC		GDTS, GDCS				
Type													L=450	L=950	L=2000	L=450	L=950	L=2000	
Raised Track	35	450	4.4	2.3								0.67							
GDTC (Steel)	40	950	7.4	2.4	20	17	14	17	10	10	1.5	0.69							
GDTS (Stainless Steel)	50	2000	8.8	2.8								0.69							
	60		11.8	3.5	28	20		24	14	12	2	1.12							
Channel	35	450	4.6	4.3				5.3	9.9	7.9	9.3	1.46							
GDCC (Steel)	40	950	5.1	7.4	30	24		8.4	13.2	11.7	13.7	1.40							
GDCS (Stainless Steel)	50	2000	6.4	8.9				10.7	16.5	14.5	16.2	1.34							
	60		7.4	11.7				12.4	19.8	18.5	20.6	1.28							

■ L Dimension Configurable with Hole Machining

Part Number	No.	L	K	P Hole Pitch	A	B	C	D	E	F	G	H	t	M	ℓ	d	d1	h	Mass (kg/m)
Raised Track	35				4.4	2.3								M4	6	-	-	-	0.67
LGTC (Steel)	40	200~2000	⊗ 0~10	50~500	7.4	2.4	20	17	14	17	10	10	1.5	M5	7.5	-	-	-	0.69
LGTS (Stainless Steel)	50		⊗ Hole=1 cannot be specified.		8.8	2.8								-	-	4.5	7.5	5	0.69
	60				11.8	3.5	28	20		24	14	12	2	-	-	5.5	9	6	1.12
Channel	35				4.6	4.3				5.3	9.9	7.9	9.3	M6	9	-	-	-	1.46
LGCC (Steel)	40	200~2000	⊗ Hole=1 cannot be specified.	50~500	5.1	7.4	30	24		8.3	13.2	11.7	13.7	-	-	4.5	7.5	5	1.40
LGCS (Stainless Steel)	50		⊗ Hole=1 cannot be specified.		6.4	8.9				10.7	16.5	14.5	16.2	-	-	5.5	9	6	1.34
	60		⊙		7.4	11.7				12.4	19.8	18.5	20.6	-	-	-	-	-	1.28

⊙ P selection is unnecessary when Number of hole is 0. ⊗ Hole machining is not applicable to Channel No. 60. ⊙ Ultra High-Molecular-Weight Polyethylene may change in dimensions as its stretch rate changes by temperature.

Ordering Example

Part Number	-	L	-	K	-	P
GDCC50	-	450	-		-	
LGTC40	-	860	-	K8	-	P100
LGCS60	-	1600	-	K0	-	


No.	Body Price				Hole Machining Charge (Body Price +)
	LGTC		LGTS		
	L200-450	L460-950	L960-1400	L1410-2000	
35					Number of Holes x200
40					
50					
60					

No.	Body Price				Hole Machining Charge (Body Price +)
	LGCC		LGCS		
	L200-450	L460-950	L960-1400	L1410-2000	
35					Number of Holes x200
40					
50					
60					



Type	Material
Raised Track	GDT
Channel	GDC

Ultra High-Molecular-Weight Polyethylene



■ L Dimension Selectable Type

Part Number	No.	L Length Selection (mm)	A	B	C	D	E	F	G	H	Mass (kg/m)	Unit Price		
												L=450	L=950	L=2000
Raised Track	40	450	7.4	2.4							0.16			
GDT	50	950	8.8	2.8	20	10	-	-	-	-	0.16			
	60	2000	11.8	3.5	25						0.36			
Channel	40	450	5.1	7.4	25	30	8.4	13.2	11.7	13.7	0.58			
GDC	50	950	6.4	8.9	30	35	10.7	16.5	14.5	16.2	0.8			
	60	2000	7.4	11.7	35	40	12.4	19.8	18.5	20.6	1.04			

⊙ Ultra High-Molecular-Weight Polyethylene may change in dimensions as its stretch rate changes by temperature.

Ordering Example

Part Number	-	L
GDT50	-	450
GDC60	-	2000