

Height Adjusting Pins

Press Fit, Counterbored


■ **Features:** Locating Pins for the height direction. Press Fit and Counterbored. O.D. and Height Configurable.

■ Press Fit



RoHS 10

Material	Surface Treatment	Hardness	Type			
			L Configurable		D and L Configurable	
			d dim. Tolerance p6	d dim. Tolerance m6	d dim. Tolerance p6	d dim. Tolerance m6
SKS3 Equivalent	-	Treated Hardness: 60 ~ 63HRC	JPAT	JPAM	JPATF	JPAMF
SKS3 Equivalent	Black Oxide	Treated Hardness: 60 ~ 63HRC	BJPAT	BJPAM	BJPATF	BJPAMF
SKS3 Equivalent	Hard Chrome Plating	Treated Hardness: 50 ~ 55HRC Plating Hardness: 750HV ~	HJPAT	HJPAM	HJPATF	HJPAMF
SUS304	-	-	SJPAT	SJPAM	SJPATF	SJPAMF
SUS40C or 13Cr stainless	-	Treated Hardness: 50 ~ 55HRC	CJPAT	CJPAM	CJPATF	CJPAMF




Ⓢ SUS304 may not be polished and may have no centering hole.

■ L Configurable

Part Number			L	D	ℓ	Unit Price					
Type	d	d dim. Tolerance m6				0.01mm Increment	JPAT	BJPAT	HJPAT	SJPAT	CJPAT
d dim. Tolerance p6	d dim. Tolerance m6	3	2.00~10.00	6	5						
		4									
		5									
		6	5.00~30.00	10	8						
		8									
		10									
		12	10.00~50.00	18	12						
		10									
		12									




Example



■ D and L Configurable

Part Number			L	D	ℓ	Unit Price					
Type	d	d dim. Tolerance m6				0.01mm Increment	1mm Increment	JPATF	BJPATF	HJPATF	SJPATF
d dim. Tolerance p6	d dim. Tolerance m6	3	2.00~10.00	5-30 (d<D<5d)	5						
		4									
		5									
		6	5.00~30.00	8							
		8									
		10									
		12	10.00~50.00	12							
		10									
		12									


■ Counterbored



RoHS 10

Material	Surface Treatment	Hardness	Type	
			L Configurable	D and L Configurable
SKS3 Equivalent	-	Treated Hardness: 60 ~ 63HRC	JPHU	JPHUZ
SKS3 Equivalent	Black Oxide	Treated Hardness: 60 ~ 63HRC	BJPHU	BJPHUZ
SKS3 Equivalent	Hard Chrome Plating	Treated Hardness: 50 ~ 55HRC Plating Hardness: 750HV ~	HJPHU	HJPHUZ
SUS304	-	-	SJPHU	SJPHUZ
SUS40C or 13Cr stainless	-	Treated Hardness: 50 ~ 55HRC	CJPHU	CJPHUZ

Ⓢ SUS304 may not be polished.



■ L Configurable

Part Number		L	D	d1	d2	H	Applicable Screw	Unit Price				
Type	No.							0.01mm Increment	JPHU	BJPHU	HJPHU	SJPHU
JPHU	3	6.00~15.00	12	3.5	6.5	4	M3					
BJPHU	4	7.00~20.00	13	4.5	8	5	M4					
HJPHU	5	8.00~20.00	15	5.5	9.5	6	M5					
SJPHU	6	9.00~25.00	20	6.5	11	7	M6					
CJPHU	8	11.00~30.00	30	9	14	9	M8					

■ D and L Configurable

Part Number		L	D	d1	d2	H	Applicable Screw	Unit Price				
Type	No.							0.01mm Increment	1mm Increment	JPHUZ	BJPHUZ	HJPHUZ
JPHUZ	3	6.00~15.00	10~15	3.5	6.5	4	M3					
BJPHUZ	4	7.00~20.00	12~20	4.5	8	5	M4					
HJPHUZ	5	8.00~20.00	15~20	5.5	9.5	6	M5					
SJPHUZ	6	9.00~25.00	15~25	6.5	11	7	M6					
CJPHUZ	8	11.00~30.00	18~30	9	14	9	M8					



Ordering Example
 Part Number - L
 JPAT8 - 15.00 (Press Fit, L Configurable)
 JPHU3 - 10.00 (Counterbored, L Configurable)

Part Number - L - D
 JPATF8 - 15.00 - 12 (Press Fit, D and L Configurable)
 JPHUZ5 - 10.00 - 20 (Counterbore, D and L Configurable)