




Thread	Type	M Material	S Surface Treatment
Coarse	AJSTR	S45C	Black Oxide
	AJSTMR	Equivalent	Electroless Nickel Plating
	AJSTRS	SUS304	-




Part Number Type	M	L 5mm Increment	d	T	MxPitch Coarse		B	D	C	E	E1	ℓ	Unit Price		
													AJSTR	AJSTMR	AJSTRS
AJSTR AJSTMR AJSTRS	4	10-50	3.5	7	4x0.7	3	5.5	5	7	2.5	2.5				
	5	10-50	4.5	9	5x0.8	4.6	7.5	10	8	3	3				
	6	15-50	5.5	9	6x1.0		8.5		10	4	4				
	8	20-50	7.5	12	8x1.25	6	11.5	15	13	5	5				

Ordering Example: Part Number - L
AJSTR4 - 20



Thread	Type	M Material	S Surface Treatment
Coarse	AJKTN	S45C	Black Oxide
	AJKTNM	Equivalent	Electroless Nickel Plating
	AJKTNS	SUS304	-
Fine	AJKTNF	S45C	Black Oxide
	AJKTNMF	Equivalent	Electroless Nickel Plating




Part Number Type	M	L 5mm Increment	d	T	MxPitch		B	D	A	F	E2	ℓ	Unit Price					
					Fine	Coarse							Coarse		Fine			
(Coarse)	3	10-45	2.5	7	-	3x0.5	3	4.5	7	10	5	4	AJKTN	AJKTNM	AJKTNS	AJKTNF	AJKTNMF	
	4	10-60	3.5	7	4x0.5	4x0.7	3	5.5	7	10	5	4						
	5	10-70	4.5	9	5x0.5	5x0.8	4.6	7.5	15	15	8	7						
	6	15-80	5.5	9	6x0.75	6x1.0		8.5										
	8	20-100	7.5	12	8x0.75	8x1.25	6	11.5										
	10	25-100	9.5	16	10x1.0	10x1.5	7	15.5										
(Fine)	12	25-150	11.5	19	12x1.0	12x1.75	7	17.5	25	20	10	9						
	16	25-150	15.5	19	-	16x2.0	8	21.5		24								

Ordering Example: Part Number - L
AJKTN10 - 80



Thread	Type	M Material	S Surface Treatment
Coarse	AJSTK	S45C	Black Oxide
	AJSTKM	Equivalent	Electroless Nickel Plating
	AJSTKS	SUS304	-



Part Number Type	M (Coarse)	L 5mm Increment	d	T	B	D	A	F	Unit Price		
									AJSTK	AJSTKM	AJSTKS
AJSTK AJSTKM AJSTKS	3	10-20	2.5	7	3	4.5	4	16			
	4	10-30	3.5	7	3	5.5	4	16			
	5	10-40	4.5	9	4.6	7.5	6	20			
	6	15-50	5.5	9	4.6	8.5	6	20			
	8	20-50	7.5	12	6	11.5					

Ordering Example: Part Number - L
AJSTK4 - 25