

Parallel Keys / Tapered Machine Keys with Gib Head


Blank Type

Parallel Keys (KET) are now on the website.

Parallel Keys - Stainless Steel



KETS



Type	Material	Tensile Strength
KETS	SUS316	600N/mm ² or More


Part Number Type	B	H	C	Unit Price	Volume Discount Rate		
				1 ~ 3 pc(s).	4~19	20~49	50~100
KETS	2	2	0.2				
	3	3					
	4	4					
	5	5					
	6	6					
	7	7	0.3				
	8	8					
	10	10					
	12	12					
	14	14					




Ordering Example

Part Number - H
KETS8 - 7

Tapered Machine Keys with Gib Head



KTH



Type	Material	Tensile Strength
KTH	S45C	600N/mm ² or More

B Dimension/H Dimension conform to B 1301-1996 (New JIS Standard).

Part Number Type	Bh9	h	L	h1	h2, f	(e)	C	Unit Price	Volume Discount Rate			
								1 ~ 4 pc(s).	5~9	10~29	30~49	
KTH	4	0	4	0	30	7	4	4	0.16~0.25			
	5	-0.030	5	0	40	8	5	5				
	6		6	-0.030	45		6	6				
	7		7.2	0	50	10	7	7	0.25~0.40			
	8	0	7	0	60	11	7	8				
	10	-0.036	8	0	75		8	10				
	12		8	-0.090	90	12	8	12				
	14		9		110	14	9	14	0.40~0.60			
	15	0	10.2	0	110	15	10	15				
	16	-0.043	10	-0.090	120	16	10	16				
	18		11	0	135	18	11	18				
	20		12	-0.110	150	20	12	20				
	22		14		170	22	14	22				
	24	0	16.2	0	180	24	16	24	0.60~0.80			
	25	-0.052	14		200	22	14	25				
	28		16	-0.110	210	25	16	28				
	32		18		240	28	18	32				
	35	0	22.3	0	260		22	35	1.00~1.20			
	36	-0.062	20		280	32	20	36				
	38		24.3	0	285	36	24	38				



Ordering Example

Part Number
KTH12



Alterations



Part Number - (LC)
KTH10 - LC60

Alteration	Code	Spec.																				
L Dimension Change 	LC	LC=1mm Increment LC (Min.) ≤ LC ≤ L For LC (Min.), see below.																				
		<table border="1"> <thead> <tr> <th>B</th> <th>LC (Min.)</th> </tr> </thead> <tbody> <tr><td>4, 5</td><td>10</td></tr> <tr><td>6, 7, 8</td><td>15</td></tr> <tr><td>10, 12</td><td>20</td></tr> <tr><td>14, 15, 16</td><td>22</td></tr> <tr><td>18, 20</td><td>25</td></tr> <tr><td>22, 24, 25</td><td>30</td></tr> <tr><td>28</td><td>35</td></tr> <tr><td>32, 35, 36</td><td>40</td></tr> <tr><td>38</td><td>45</td></tr> </tbody> </table>	B	LC (Min.)	4, 5	10	6, 7, 8	15	10, 12	20	14, 15, 16	22	18, 20	25	22, 24, 25	30	28	35	32, 35, 36	40	38	45
B	LC (Min.)																					
4, 5	10																					
6, 7, 8	15																					
10, 12	20																					
14, 15, 16	22																					
18, 20	25																					
22, 24, 25	30																					
28	35																					
32, 35, 36	40																					
38	45																					