

# Mini Rods

O.D. Tolerance Selectable

O.D. Selectable	O.D. Configurable	Material	Hardness
KRSH	KRBSH	SKH51	58HRC~
KRSK	KRBSK	SUJ2	
KRSD	KRBSD	SKD11	60HRC~
KRSS	KRBSS	SUS440C	56HRC~
KRSG	KRB SG	SUS304	-

  

D	Tolerance Selection				
	M	P	G	H	S
0.30	+0.008	+0.012	-0.002	0	0
3.00	+0.002	+0.006	-0.008	-0.010	
3.01	+0.012	+0.020	-0.004	0	-0.01
5.00	+0.004	+0.012	-0.012	-0.012	

  
  

C Dimension		
or More	or Less	C
D0.3	D0.59	Deburring
D0.6	D5	0.1

  

L Dimension Tolerance		
or More	or Less	Tolerance
5.0	6.0	±0.1
6.1	30.0	±0.2
30.1	120.0	±0.3
120.1	150.0	±0.5

## O.D. Selectable

Part Number		L 0.1mm Increment	Unit Price				
Type	Tolerance Selection		KRSH	KRSK	KRSD	KRSS	KRSG
<b>KRSH</b> (D0.3~5) <b>KRSK</b> (D0.5~5) <b>KRSD</b> (D1~5) <b>KRSS</b> (D0.3~5) <b>KRSG</b> (D1~5)	M	0.3					
		0.4					
		0.5					
		0.6					
		0.7	5.0~50.0				
		0.8					
		0.9					
		1					
		1.1					
		1.2					
	G H	1.3	5.0~60.0				
		1.4	5.0~70.0				
		1.5	5.0~75.0				
		1.6	5.0~80.0				
		1.8	5.0~90.0				
		1.9					
		2	5.0~100.0				
		2.5					
		3					
		3.5	5.0~150.0				
4							
4.5							
5							



**O.D. Selectable**  
**Part Number** - L  
**Type** | **D Tolerance** | **D** - L  
 KRSH | M | 0.5 - 50.0

**O.D. Configurable**  
**Part Number** - L - D  
**Type** | **D Tolerance** | **No.** - L - D  
 KRBSH | H | 0.6 - 30.0 - D0.55

## O.D. Configurable (0.01mm Increment)

Part Number		L 0.1mm Increment	D 0.01mm Increment	Unit Price				
Type	Tolerance Selection			No.	KRBSH	KRBSK	KRBSD	KRBSS
<b>KRBSH</b> (No.0.5~5) <b>KRBSK</b> (No.0.6~5) <b>KRBSD</b> (No.1.5~5) <b>KRBSS</b> (No.0.5~5) <b>KRBSG</b> (No.1.5~5)	M P G H S	0.5	0.30~0.49					
		0.6	0.50~0.59					
		1	0.60~0.99					
		1.5	1.00~1.49					
		2	1.50~1.99					
		2.5	2.00~2.49					
		3	2.50~2.99					
		3.5	3.00~3.49					
		4	3.50~3.99					
		4.5	4.00~4.49					
5	4.50~4.99							



**Alterations** **Part Number** - L - (AC, LKC)  
 KRSHM0.5 - 50.0 - LKC

Alterations	Point Taper	L Dimension Tolerance
<b>Code</b>	AC	LKC
<b>Spec.</b>	AC: 0.1mm Increment. ● 0.5≤AC≤10.0 ● D-2(AC tan15°)≥0.2 ● One end only is tapered. [Ordering Code] AC 5.5	Changes L dimension tolerance within ±0.05 [Ordering Code] LKC