

Strut Clamps / Bar Clamps

Arm

■ **Features:** Combined with Strut Clamps, mounted posts can be adjusted in a circumferential direction.

Strut Clamps

RoHS10

Type	Material	Surface Treatment	Accessory
KLKA	Steel for General	Black Oxide	Hex Socket Head Cap Screw
MKA	Structure	Electroless Nickel Plating	
ALKA	Aluminum Alloy	Black Anodize	
SLKA	SUS304	-	

⚠ Accessories: CB screws are included with black oxide coating and black anodized products, and SCB screws are included with electroless nickel plating products.

6.3 / (6.3 / 1.6 /)

D8-25


D30, 35

⚠ For P Dimension 50 or more, a centering hole may remain at the end of D1.

Part Number	Type	DH7	P Selection	D1g6	Included Screw										Unit Price					
					A	B	E	H	M	d	d1	Z	S	W	KLKA	MKA	ALKA	SLKA		
KLKA MKA ALKA SLKA (D≤30)	8	+0.015	12 30 50	8	-0.005	7	12	10.5	7	M3	3.5	6	3	2	M3- 8, 1 pc. M4- 8, 1 pc. M4-10, 1 pc. M4-15, 1 pc. M4-20, 1 pc. M5-25, 1 pc. M5-30, 2 pcs. M5-35, 2 pcs.					
	10	0	13 30 50	10	-0.014	9	13	13	9	M4	4.5	7.5	4							
	12	+0.018		12	-0.006	11	15	14.5	10											
	15	0	19 30 50	15	-0.017	12	19	15	10.5	M5	5.5	9	5							
	20	+0.021	25 50 70	20	-0.007	15	25	17.5	13											
	25	0	30 50 70	25	-0.020	18	30	21	16	M6	6.6	11	6.5							
	30	+0.025	35 50 70	30	-0.009	21	36	23.5	18.5											
	35	0	40 70 90	35	-0.025	24	40	26.5	21											

⚠ D Dimension for SLKA is available up to 30. ⚠ DH7 tolerance is before the slit machining. ⚠ For mating, g6, f8 shaft tolerances are recommended. Tightening with a long wrench is recommended.

Ordering Example: Part Number **MKA10** - P **30**



■ **Features:** Bar Clamps can be used as a guide handle in combination with Strut Clamps.

Bar Clamps

RoHS10

Type	Material	Surface Treatment	Accessory
BCLB	SS400	Black Oxide	Hex Socket Head Cap Screw
BCLM		Electroless Nickel Plating	
BCLA	A6063	Black Anodize	
BCLS	SUS304	-	

* Included Screw: Black oxide and black anodize products have screw of same surface treatment, and electroless nickel plating and SUS products have stainless screw.

6.3 / (6.3 / 1.6 /)

Included Screw

D	Screw Size
6	M3-8
8	M4-8
10	M5-10
12	M5-10
13	M5-15
15	M6-15
16	M6-15
20	M6-20

⚠ For L Dimension 50 or more, a centering hole may remain at the end of D1.

Part Number	Type	DH7	L Selection	B	D1g6	Included Screw										Unit Price			
						G	E	C	H	M	d	d1	Z	J	BCLB	BCLM	BCLA	BCLS	
BCLB BCLM BCLA BCLS	6	+0.012	25 40	12	8	-0.005	14	1	1	8	M3	3.4	6.5	3.5	17				
	8	+0.015		14	10	-0.014	15	1.5		9	M4	4.5	8	4.5	19				
	10	0	30 50	16	12		16	2		10						22			
	12			18	12	-0.006	17	2.5		11	M5	5.5	9.5	5.5	24				
	13	+0.018	50 70	20	15	-0.017	17	2.5		11						27			
	15	0		23	16		19	2.5		12						31			
	16	+0.021		25	20	-0.007	20	3		13	M6	6.6	11	6.5		34			
	20	0		30	20	-0.020	21			14						35			

⚠ Dir tolerance is before the slit machining.

Ordering Example: Part Number **BCLB16** - L **70**