



Sponge Washers


Standard		Configurable Type		Material	Hardness	Color
No Adhesive	Adhesive	No Adhesive	Adhesive			
WSGC	WSGCA	WSGNC	WSGNCA	Chloroprene Rubber Sponge	Asker C25	Black
WSGP	WSGPA	WSGNP	WSGNPA	Ethylene Rubber Sponge	Asker C8	Black
WSGB	WSGBA	WSGNB	WSGNBA	Nitrile Rubber Sponge	Asker C30	Black
WSEA	WSEAA	WSEPA	WSEPA	EPT Sealer®	(Asker C5 or Less)	Black
WSGA	WSGAA	WSGNA	WSGNAA	Silicon Rubber Sponge	Asker C35	Orange
WSGF	WSGFA	WSGNF	WSGNFA	Fluororubber Sponge	Asker C35	Black





(No Adhesive) (Adhesive) Adhesive Seal (Thickness 0.14 - 0.2mm)

$D \pm 0.5$ $T \pm 0.5$

For EPT Sealer® (Dust-proof, General Purpose Sponge), see  **P.445**.
 Temperature limit for seals is 80°C.

D, V Tolerance		
D, V	Tolerance	
10-40	±1.0	
41-60	±1.5	
61-100	±2.0	

Standard Type (No Adhesive)

Part Number	Type	D	V Selection	T Selection	Unit Price					
					WSGC	WSGP	WSGB	WSEA	WSGA	WSGF
WSGC WSGP WSGB WSEA WSGA WSGF	6	2		3						
	8	2 3 4		3						
	10	3 4 5 6		3 5						
	12	4 5 6 8		3 5						
	15	4 5 6 8 10		3 5						
	20	5 6 8 10 12		3 5 10						
	25	5 6 8 10 12 16 20		3 5 10						
	30	5 6 8 10 12 16 20		3 5 10						
	35	8 10 12 16 20 25		5 10						
	40	8 10 12 16 20 25 30		5 10						
	50	8 10 12 16 20 25 30		5 10						
	60	12 16 20 25 30 40		5 10						

Standard Type (Adhesive)

Part Number	Type	D	V Selection	T Selection	Unit Price					
					WSGCA	WSGPA	WSGBA	WSEAA	WSGAA	WSGFA
WSGCA WSGPA WSGBA WSEAA WSGAA WSGFA	6	2		3						
	8	2 3 4		3						
	10	3 4 5 6		3 5						
	12	4 5 6 8		3 5						
	15	4 5 6 8 10		3 5						
	20	5 6 8 10 12		3 5 10						
	25	5 6 8 10 12 16 20		3 5 10						
	30	5 6 8 10 12 16 20		3 5 10						
	35	8 10 12 16 20 25		5 10						
	40	8 10 12 16 20 25 30		5 10						
	50	8 10 12 16 20 25 30		5 10						
	60	12 16 20 25 30 40		5 10						

Configurable Type

The unit price of Configurable Type "No Adhesive" is shown in the table below.

Part Number		T	T Tolerance	D 1mm Increment	V 1mm Increment	Unit Price					
Type (xMaterial Multiplier)						D10-20	D21-40	D41-60	D61-80	D81-100	
WSGNC (x1.0) WSGNP (x1.0) WSGNB (x1.0) WSEPA (x1.0)	WSGNCA (x1.2) WSGNPA (x1.2) WSGNBA (x1.2) WSEPA (x1.2)	3	±0.5	10-100	0 (No Hole) 5-30 When D≤40, D-V≥5 When D>40, D-V≥8						
		5									
		8									
		10									
WSGNA (x1.0) WSGNAA (x1.2)		3	±0.5								
		5									
		8									
WSGNF (x1.0) WSGNFA (x1.2)		2	±0.5								
		3									
		5									
	10	±1.5									



Ordering Example

Standard

Part Number - V - T

WSGPA15 - 6 - 5

Configurable Type

Part Number - D - V

WSGNA3 - D12 - V6