

Caster / Angle Mount

Light Load

Light Load

(Rubber)

(Urethane)

RoHS 10

Swivel with Stopper **CLGS**

Main Body		Wheel			Bearing	
M	S	M	Material (Color)	Swiveling Part	Wheel	
SPHC	Trivalent Chromate	Synthetic Rubber (Black), Nylon (White), Urethane (Brown), FC250 (Gray)		Incorporated		None

Main Body	Part Number Type	D	Wheel Material	H	A	C	F1	F2	d	B	r	E	t	Allowable Load (N)				Mass (g)			
														R	N	U	G	R	N	U	G
Swivel	CLGJ	25	R (Rubber)	35	35	30	28	23	4.2	12	21	8	1.6	80	100	100	120	35	30	40	53
		32		42	38	32	30	24	14	27	10	1.6	120	180	180	200	50	40	50	68	
		38		50	46	38	36	28	5.3	17	32	12	1.6	200	280	280	300	80	75	80	116
		50		65	59	47	46	35	6.5	20	42	16	2	300	380	380	400	140	110	119	213
		65		75	70	58	55	42	8.8	25	53	19	2.3	400	550	550	600	245	180	195	450
Fixed	CLGK	25	N (Nylon)	35	36	18	29	-	4.2	12	-	-	1.6	80	100	100	120	25	23	31	47
		32		42	20	29	-	4.2	14	-	1.6	120	180	180	200	38	30	40	58		
		38		50	46	25	36	15	5.3	17	-	1.6	200	280	280	300	63	48	52	106	
		50		65	58	40	45	25	6.5	20	-	2	300	380	380	400	130	95	110	220	
		65		75	70	47	55	28	8.8	25	-	2.3	400	550	550	600	240	175	190	395	
Swivel with Stopper	CLGS	50	G (Casting)	65	59	47	46	35	6.5	20	44	16	2	300	380	380	500	165	135	145	420
		65		80	70	58	55	42	8.8	25	58	19	2.3	400	550	550	600	280	215	230	485
		75		90	70	58	55	42	8.8	26	58	19	2.3	500	650	650	700	290	195	215	530
		50		65	59	47	46	35	6.5	20	44	16	2	300	380	380	500	165	135	145	420
		65		80	70	58	55	42	8.8	25	58	19	2.3	400	550	550	600	280	215	230	485

Ordering Example: Part Number **CLGJ38** - Wheel Material **R**

Part Number Type	D	Unit Price			
		R	N	U	G
CLGJ	25				
	32				
	38				
	50				
	65				
CLGK	25				
	32				
	38				
	50				
	65				
CLGS	50				
	65				
	75				

Angle Mount

(Angle Mount)

(Angle Mount with Stopper)

RoHS 10

Swivel with Stopper **CNGAS**

⚠ Ensure that vertical load is applied to the mounting surface. Applying load on the outside of angle may cause deformation and breakage.

Main Body		Wheel			Bearing	
M	S	M	Material (Color)	Swiveling Part	Wheel	
SPHC	Trivalent Chromate	Synthetic Rubber (Black), Nylon (White)		Incorporated		None

Mount Type	Part Number Type	D	Wheel Material	H	B	E	r	Allowable Load (N)	Mass (g)	Unit Price	
										R	N
Angle Mount	CNGA	50	R (Rubber)	65	20	22	47	300	200		
		65		82	21	23	56	400	270		
		75		92	21	27	65	400	310		
Angle Mount with Stopper	CNGAS	50	N (Nylon)	65	20	22	49	300	210		
		65		82	21	23	56	400	285		
		75		92	21	27	65	400	330		

Ordering Example: Part Number **CNGA50** - Wheel Material **R**