

# Mounting Plates / Mounting Nuts / Protection Caps for Leveling Mounts

**Economy Type**

**FJKMT**

**RoHS 10**

**M** Material: SS400  
**S** Surface Treatment: Bright Chromate Plating

Part Number		A	B	L	Unit Price
Type	No.				1 ~ 100 pcs.
FJKMT	12	22.5	19.3	95	
	16	25	24.5		
	20	28	31.0		

Ordering Example: Part Number **FJKMT12**

For orders larger than indicated quantity, please check with WOS.

**Hold Down Plates for Leveling Mounts - Thick Type**

Steel: **AJPNF**, **AJKNF**  
Stainless Steel: **AJPNFS**, **AJKNFS**


**RoHS 10**

Type	M	S
AJPNF, AJKNF	SS400	Trivalent Chromate
AJPNFS, AJKNFS	SUS304	-

Plate thickness may vary up to -10%.

Part Number Type	No.	t Plate Thickness	D	A	B	K	C	L	L1	Applicable Leveling Mount	Unit Price	
											Steel	Stainless Steel
AJPNF (Steel)	16	4.5	29	37.5	17	50	28.5	115	72	NFJN16 (P.1107)		
	20	4.5	36	45.5	21	60	28.5	125	77.5	NFJN20 (P.1107)		
AJKNF (Steel)	16	4.5	29	37.5	17	50	24.5	115	72	FJFN16 (P.1110)		
	20	4.5	36	45.5	21	60	24.5	125	77.5	FJFN20 (P.1110)		

Ordering Example: Part Number - t  
AJPNF20 - 4.5



Hold Down plates may not be used at 4 places depending on installation conditions of equipment and machines. In that case, using Thick Type prevents disengagement and displacement, and produces equivalent effects with fewest mounting plates.

**Hold Down Plates for Leveling Mounts**

Steel: **FJKPF**, **FJKPN**, **FJKPG**  
Stainless Steel: **FJKPFS**, **FJKPNS**, **FJKPGS**

**RoHS 10**

Type	M	S
FJKP	SS400	Trivalent Chromate
FJKP	SUS304	-

Part Number Type	No.	t Thickness		A	B	C	L	L1	Applicable Leveling Mount	Unit Price		
		FJKP	FJKP							S		
FJKPF (Steel)	12	2	2	22.5	19	22	95	65	NFJN12 (P.1107)			
	16						130	100				
	20						95	65		NFJN16 (P.1107)		
	20L						130	100				
FJKPN (Steel)	12	2	2	22.5	19	20	95	65	FJFN12 (P.1110)			
	16						130	100				
	20						95	65		FJFN16 (P.1110)		
	20L						130	100				
FJKPG (Steel)	12	2	2	22.5	19	25	95	65	FJGN12 (P.1108)			
	16						130	100				
	20						95	65		FJGN16 (P.1108)		
	20L						130	100				

For FJKPN and FJKPNS, t=2 when t dimension is not specified.

Ordering Example: Part Number - t  
FJKPN16 - 3.2

**Mounting Nuts for Leveling Mounts**

**FJTP**


**RoHS 10**

**Features**  
Hex nuts do not fall off as they are swaged on.

**M** Material: SS400  
**S** Surface Treatment: Trivalent Chromate

Part Number Type	M (Coarse)	B	C	D	E	F	G	d	Unit Price
FJTP	12	40	40	28	28	2	10	6	
		60		42	22				
		80		36	36				
	16	50	50	56	26	3	13	8	
		80		36	36				
		80		56	26				

Ordering Example: Part Number - B  
FJTP16 - 80



**Protection Caps for Leveling Mounts**

**AJCP**

**RoHS 10**

20 pcs. per pkg. **M** Material: EPDM

Part Number Type	No.	Color	D	L	d1	d2	Ø1	Ø2	Applicable Screw Size (Coarse Thread)	Unit Price	Volume Discount Rate
AJCP	8	B (Black)	11	35	5.5	7	10	20	M6, 8		10-20
	12		16.5		9.5	11.5			M10, 12		
	20		24.5		15.5	19.5			M16, 20		

Ordering Example: Part Number - Color  
AJCP12 - B

Mounting on Tip of Leveling Mounts

Example: Can be used to protect exposed threaded portions. Select according to size of M threads. Easy installation due to its flexibility.

