

Leveler Bolts

Tip SR Square Chamfered

Coarse / Fine

Type	L Fixed	L Selectable	Material	Hardness (Tip Induction Hardened)	Surface Treatment
FJKB	FJKB	FJKB	S45C	50~56HRC	Trivalent Chromate
FJKB (Fine)	-	-	-	-	-
FJKB	-	-	SUS304	-	-

Tip SR Square Chamfered Type

Type	Part Number		l	d	E	F	H	SR	J	K	r	B	(e)	T	Load Capacity (kN)	Mass (g)
	M (xP)	Coarse														
FJKB	12 (x1.75)	-	10	8	6	1	8	8	8	10	0.5	19	21.9	10	23.6	75
FJKB (Stainless Steel)	16 (x2.0)	-	12	13	-	1.6	10	14	10	13	1.0	24	27.7	13	44.0	171
FJKB	20 (x2.5)	20 (x1.5)	13.5	15	6.5	2	12	16	12	16	-	30	34.6	16	68.6	252
FJKB (Fine)	24 (x3.0)	24 (x1.5)	14	18	8	2.5	14	18	14	18	1.2	36	41.6	19	98.8	436
FJKB (Fine)	-	30 (x1.5)	16	22	10	3	17	24	16	25	1.2	46	53.1	24	123.3	680

L Fixed Type

Type	Part Number		L	Unit Price		
	M (xP)	Coarse		Fine	FJKB	FJKBS
FJKB	12 (x1.75)	-	80	-	-	-
FJKB (Stainless Steel)	16 (x2.0)	-	98	-	-	-
FJKB	20 (x2.5)	20 (x1.5)	100	-	-	-
FJKB (Fine)	24 (x3.0)	24 (x1.5)	112	-	-	-
FJKB (Fine)	-	30 (x1.5)	130	-	-	-

L Selectable Type

Type	Part Number		L			Unit Price
	M (xP)	Coarse	Fine	Fine	Fine	
FJKB	12 (x1.75)	60	100	-	-	-
	16 (x2.0)	80	100	120	-	-
	20 (x2.5)	-	-	120	-	-

Tip SR Hex Chamfered

Coarse

Type	L Fixed	L Selectable	Material	Hardness (Tip Induction Hardened)	Surface Treatment
FJKC	FJKC	FJKC	S45C	-	Trivalent Chromate
FJKC	-	-	SUS304	-	-

Tip SR Hex Chamfered Type

Type	Part Number		A	B	d	SR	(e)	T	Load Capacity (kN)	Mass (g)
	M (xP)	Coarse								
FJKC	12 (x1.75)	-	8	19	8	8	21.9	10	7.1	100
FJKC (Stainless Steel)	16 (x2.0)	-	10	24	13	14	27.7	13	9.8	200
FJKC	20 (x2.5)	20 (x1.5)	13	30	15	16	34.6	16	21.0	300

L Fixed Type

Type	Part Number		L	Unit Price	
	M (xP)	Coarse		Fine	FJKC
FJKC	12 (x1.75)	-	136	-	-
	16 (x2.0)	-	-	-	-
	20 (x2.5)	-	-	-	-

L Selectable Type

Type	Part Number		L			Unit Price
	M (xP)	Coarse	Fine	Fine	Fine	
FJKCF	12 (x1.75)	60	80	100	-	-
	16 (x2.0)	80	100	120	-	-
	20 (x2.5)	-	-	100	120	-
	-	-	-	-	-	-

Flanged Tip SR

Coarse

Type	L Fixed	L Selectable	Material	Hardness (Tip Induction Hardened)	Surface Treatment
-	-	FJKF	S45C	50~56HRC	Trivalent Chromate

Flanged Tip SR Type

Type	Part Number		L			L1	d	E	(e)	SR	r	B	T	Load Capacity (kN)	Mass (g)	Unit Price
	M (xP)	Coarse	Fine	Fine	Fine											
FJKF	12 (x1.75)	60	80	100	-	20	12	6	21.9	10	1	19	10	23.6	110	-
	16 (x2.0)	80	100	120	-	25	16	8	27.7	14	2	24	13	44.0	210	-
	20 (x2.5)	100	120	-	-	34	20	10	34.6	16	2	30	16	68.6	315	-

Flanged Tip Sphere

Coarse

Type	L Fixed	L Selectable	Material	Hardness (Tip Induction Hardened)	Surface Treatment
-	-	FJKM	S45C	50~56HRC	Trivalent Chromate

Flanged Tip Sphere Type

Type	Part Number		L			L1	d	E	(e)	R	r	B	T	Load Capacity (kN)	Mass (g)	Unit Price
	M (xP)	Coarse	Fine	Fine	Fine											
FJKM	12 (x1.75)	60	80	100	-	24	12	12	21.9	6	1	19	10	23.6	115	-
	16 (x2.0)	80	100	120	-	30.5	16	13.5	27.7	8	2	24	13	44.0	215	-
	20 (x2.5)	100	120	-	-	36.5	20	14.5	34.6	10	2	30	16	68.6	320	-

Ordering Example: Part Number - L
FJKB12 - 80
FJKCF16 - 80