



Aluminum Type

HHDNFA

ex Example

Material: Aluminum Alloy
Surface Treatment: Baked Paint

RoHS 10

Part Number		Allowable Load (N)	Mass (g)	Unit Price
Type	L			
HHDNFA	112	1100	105	

Cast Offset

UWASNDF

Material: SUS304 Equivalent
Surface Treatment: Buffing

RoHS 10

Part Number		L1	Allowable Load (N)	Mass (g)	Unit Price
Type	L				
UWASNDF	80	98	500	100	
	100	118		110	
	150	168		130	

Ordering Example
 Part Number
HHDNFA112
UWASNDF100

Aluminum Tube Pull Handles

UHFAP
UHFAPFC (L Configurable)

RoHS 10

Part Name	Material
Tube Handle	A6063
Elbow	Glass Fiber Reinforced Nylon

Small Diameter Aluminum Tube

UHFAPC
UHFAPFC (L Configurable)

RoHS 10

Part Name	Material
Tube Handle	A6063
Elbow	Polycarbonate

L Fixed				L Configurable			
Part Number	L	Applicable Screw	Unit Price	Part Number	L 1mm Increment	Applicable Screw	Unit Price
UHFAP (L Fixed)	150	Flat Head Screw M8		UHFAP (L Configurable)	100-150	Flat Head Screw M8	
	200		151-200				
	250		201-250				
	300		251-300				
	400		301-400				
	500		401-500				
	600		501-600				

L Fixed				L Configurable			
Part Number	L	Applicable Screw	Unit Price	Part Number	L 1mm Increment	Applicable Screw	Unit Price
UHFAPC (L Fixed)	100	Hex Socket Head Cap Screw M6		UHFAPFC (L Configurable)	100-150	Hex Socket Head Cap Screw M6	
	150		151-200				
	200		201-250				
	250		251-300				
	300						

Ordering Example
 Part Number - L
UHFAP 150 ⚠️ "-" is not necessary for L Fixed Type.
UHFAPFC - 225