

Covered Draw Latches / Draw Latches for Medium Loads

Covered Draw Latches RoHS10

PKCS1

<Recommended Mounting Hole Pitch>

PKCS2

<Recommended Mounting Hole Pitch>

PKCS3

<Recommended Mounting Hole Pitch>

* The dimensions are for 0mm tightening amount.

Part Number		* Pull Force N(kgf)	Mass (g)	Unit Price 1 ~ 9 pc (s)	Volume Discount Rate 10~50
PKCS	1	12 (1.2)	25		
	2	69 (7)	53		
	3	81 (8.3)	115		

Material Surface Treatment
 SUS304 Tumble Polish

Part Number Type	No.	* Pull Force N(kgf)	Mass (g)	Unit Price 1 ~ 9 pc (s)	Volume Discount Rate 10~50
PKCS	1	12 (1.2)	25		
	2	69 (7)	53		
	3	81 (8.3)	115		

Stainless Steel Draw Latches for Medium Loads RoHS10

PKWSA

<Recommended Mounting Hole Pitch>

* The dimensions are for 0mm tightening amount.

Part Number Type	No.	* Pull Force N (kgf)	Mass (g)	Unit Price 1 ~ 9 pc (s)	Volume Discount Rate 10~29	30~49	50~200
PKWSA	1	245 (25)	80				

Material Surface Treatment
 SUS304 Tumble Polish

Part Number Type	No.	* Pull Force N (kgf)	Mass (g)	Unit Price 1 ~ 9 pc (s)	Volume Discount Rate 10~29	30~49	50~200
PKWSA	1	245 (25)	80				

Ordering Example Part Number
PKWSA1

Draw Latches for Medium Loads RoHS10

PKWSZ

<Recommended Mounting Hole Pitch>

* The dimensions are for 0mm tightening amount.

Part Number Type	No.	* Pull Force N (kgf)	Mass (g)	Unit Price 1 ~ 9 pc (s)	Volume Discount Rate 10~29	30~49	50~200
PKWSZ	1	245 (25)	79				

Material Surface Treatment
 SPCC Trivalent Chromate

Part Number Type	No.	* Pull Force N (kgf)	Mass (g)	Unit Price 1 ~ 9 pc (s)	Volume Discount Rate 10~29	30~49	50~200
PKWSZ	1	245 (25)	79				

Ordering Example Part Number
PKWSZ1