



Manifold Blocks - Pneumatic

Lateral and Vertical Through Hole / Lateral Through Hole, Upper Hole



For details of recommended tapered male thread tightening torque and through pilot hole, see P.1224.

Manifold Blocks - Pneumatic

RoHS10

BMIAN

2-Ø5.5 Through
Ø9.5 Counterbore, Depth 5.5

3-Ø5.5 Through
Ø9.5 Counterbore, Depth 5.5

2-Ø5.5 Through
Ø9.5 Counterbore, Depth 5.5

2-Ø5.5 Through
Ø9.5 Counterbore, Depth 5.5

2-Ø5.5 Through
Ø9.5 Counterbore, Depth 5.5

2-Ø5.5 Through
Ø9.5 Counterbore, Depth 5.5

Thread: JIS B0203 Rc(PT) Material: Aluminum Alloy

Manifold Blocks - Pneumatic

RoHS10

BMSLN

2-Ø6.6 Through
Ø11 Counterbore, Depth 6.5

3-Ø6.6 Through
Ø11 Counterbore, Depth 6.5

2-Ø6.6 Through
Ø11 Counterbore, Depth 6.5

2-Ø6.6 Through
Ø11 Counterbore, Depth 6.5

2-Ø6.6 Through
Ø11 Counterbore, Depth 6.5

(Max. Operating Pressure: 1MPa≈10kgf/cm² or less)

Thread: JIS B0203 Rc(PT) Material: Aluminum Alloy

Type	Part Number		d1 Rc(PT)	d2 Rc(PT)	Unit Price
	No.				
BMIAN	1	11	1/8	1/8	
		22	1/4	1/4	
	2	11	1/8	1/8	
		22	1/8	1/4	
	3	11	1/8	1/8	
		22	1/4	1/4	
4	11	1/8	1/8		
	22	1/4	1/4		
5	12	1/8	1/4		
	22	1/4	1/4		
6	11	1/8	1/8		

Type	Part Number		d1 Rc(PT)	d2 Rc(PT)	Unit Price
	No.				
BMSLN	2	24	1/4	1/2	
		33	3/8	3/8	
		44	1/2	1/2	
		33	3/8	3/8	
4	4	23	1/4	3/8	
		24	1/4	1/2	
		33	3/8	3/8	
		44	1/2	1/2	
5	5	24	1/4	1/2	
		33	3/8	3/8	
		44	1/2	1/2	
6	23	1/4	3/8		

Ordering Example Part Number
BMIAN3-22