



# A Dimension Configurable Plates - Duralumin

## A2017P (Al-Cu Aluminum Alloy)




4-Surface Milled (Rolled)



RoHS10

ALDS  
ALD  
ALDT



Part Number - **A - B - T**  
ALD - 300 - 100 - 15

(Ex.) For ALD-300-100-15

A Dimension x Area Unit Price = Price

Part Number	A: 1mm Increment	B: 1mm Increment	Unit Price					
			T5, 6	T8, 10	T12, 15	T20	T25	T30
ALDS (Configurable Size)	25~50	25~50						
	51~75	25~50						
	76~100	51~75	25~50					
		25~50	51~75					
		51~75	51~75					
		76~100	76~100					

Part Number	A: 1mm Increment	B	T	Unit Price											
				5	6	8	10	12	15	20	25	30	35	40	
ALD (Configurable Size)	100~200	100	5												
	201~300														
	301~500														
	101~250	125													
	251~500														
	126~300	150													
	301~500														
	151~300			160											
	301~500														
	161~500	200													
201~500	250														
251~500	300														
ALDT (Configurable Size)	501~800	125													
	501~800	150													
	501~800	160													
	501~800	200													
	501~800	250													
	501~800	300													
	350~1200	350													
	400~1200	400													
	450~1200	450													
	500~1200	500													
	600~1200	600													
	800~1200	800													



Alterations



Part Number - **A - B - T** -(BC, CCA...etc.)  
ALD - 315 - 200 - 20 - BC176

### Precision Standards

- Flatness 2 or Less per 1000mm
- T Dimension Tolerance
 

5	6	8	10	12, 15	20	25	30, 35	40
±0.35	±0.45	±0.5	±0.6	±0.7	±0.8	±0.9	±1.0	±1.1
- A, B Dimension Tolerance
 

25~100	101~250	251~1000	1001~
±0.2	±0.25	±0.4	±1.0
- Perpendicularity of Datum Plane 0.015 or less per 100mm
- Circumference Chamfering C0.3 or Less

Alterations	Code	Spec.
Width (B Dimension) 	BC	Cuts B dimension. BC=1mm Increment Ordering Code BC195 BC196 ALD 26≤BC≤B-1 ALDT 126≤BC≤B-1 Applicable to ALD and ALDT only.
Corner Cut 	CCA CCB CCC CCD	Cuts any corners. 1≤ Corner Cut ≤10 1mm Increment Ordering Code (Ex.)When the corners of A and D are cut by C5, →CCA5-CCD5